





ROHS




NOTES:

1.ELECTRICAL CHARACTERS:

- 1-1.RATING: DC 30V 0.5A;
- 1-2.CONTATCT RESISTANCE: $\leq 30m\Omega$;
- 1-3.INSULATION RESISTANCE: $\geq 100M\Omega$ DC 500V;
- 1-4.WITHSTANDING VOLTAGE: AC 500V 1min;
- 1-5.LIFE: 5,000 CYCLES;

2.MECHANICAL CHARACTERISTICS:

- 2-1.INSERTION&EXTRACTION FORCE: 3~30N;
- 2-2.OPERATING TEMPERATURE: $-30^{\circ}C \sim +70^{\circ}C$;



⑥	PIN		1	BRASS	CuSn PLATED
⑤	TERMINAL	3	1	BRASS t=0.3	CuSn PLATED
④	BREAK TERMINAL	2	1	BRASS t=0.3	CuSn PLATED
③	TIP SPRING	1	1	BRONZE t=0.25	SnSb PLATED
②	COVER		1	PBT	BLACK
①	HOUSING		1	PBT	BLACK
No.	PART NAME	TER'NO.	Q'TY	MATERIAL	REMARK

COSTOMER DRAWING		LAILAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECK					
APPROVAL					
TOLERANCES ARE					
30-150	±0.35	ANGLE			
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
		±3°			
TITLE		DC电源连接器D6. 3C2. 0(直插)		REV.	A
PART NO.		LAIL-DC30-D6. 3C2. 0G-L		UNITS	mm
DWG.NO.				Projection	