




ROHS




FRONT VIEW




RIGHT SIDE VIEW



BOTTOM VIEW



A(2:1)

RECOMMENDED PCB LAYOUT
VIEWED FROM COMPONENT SIDE

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

MATERIAL:

HOUSING: PBT,UL94V-0,BLACK.

TERMINAL: PHOSPHOR BRONZE $\phi=0.46\text{MM.G/FU}$ GOLD PLATING

MECHANICAL:

DURABILITY: 750 CYCLES MIN.

MATING FORCE: 2.2KG.F MAX.

RETENTION STRENGTH : 7.7KG.F BETWEEN JACK AND PLUG.

OPERATING TEMPERATURE: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.STORAGE TEMPERATURE: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.

ALL CRITICAL DIMENSIONS WITH "*"

ELECTRICAL:

VOLTAGE: 125 VOLTS AC.

CURRENT RATING:1.5AMP

DIELECTRIC STRENGTH: 1000 VAC RMS 50HZ OR 60HZ.1MIN

INSULATION RESISTANCE: 500 MEGA OHMS MIN.INITIAL

AFTER 500V DC FOR 1 MINUTE

CONTACT RESISTANCE: SINGLE TERMINAL 50 MILLIOHMS MAX

INITIAL 50 MILLIOHMS MAX.

AFTER DURABILITY TEST.



CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECKED					
APPROVED					
TOLERANCES ARE		TITLE	1* 6P6C 无耳朵 全塑	REV.	A
30-150	±0.35	PART NO.	LAIL-RJ11-LED0-BN-01G-WC	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1	DWG. NO.		Projection	