

A		B		C		D		E	
REV.		DESCRIPTION		ECN NO.		NAME		DATE	

PIN NO		PIN	DIM A	DIM B	DIM C	DIM D	DIM E
B0510MAA10-8P		8	1.50	2.50	4.70	3.40	4.00
B0510MAA10-10P		10	2.00	3.00	5.20	3.90	
B0510MAA10-12P		12	2.50	3.50	5.70	4.40	
B0510MAA10-14P		14	3.00	4.00	6.20	4.90	
B0510MAA10-16P		16	3.50	4.50	6.70	5.40	
B0510MAA10-18P		18	4.00	5.00	7.20	5.90	
B0510MAA10-20P		20	4.50	5.50	7.70	6.40	
B0510MAA10-22P		22	5.00	6.00	8.20	6.90	
B0510MAA10-24P		24	5.50	6.50	8.70	7.40	
B0510MAA10-26P		26	6.00	7.00	9.20	7.90	
B0510MAA10-28P		28	6.50	7.50	9.70	8.40	8.00
B0510MAA10-30P		30	7.00	8.00	10.20	8.90	
B0510MAA10-32P		32	7.50	8.50	10.70	9.40	
B0510MAA10-34P		34	8.00	9.00	11.20	9.90	
B0510MAA10-36P		36	8.50	9.50	11.70	10.40	
B0510MAA10-38P		38	9.00	10.00	12.20	10.90	
B0510MAA10-40P		40	9.50	10.50	12.70	11.40	
B0510MAA10-44P		44	10.50	11.50	13.70	12.40	
B0510MAA10-50P		50	12.00	13.00	15.20	13.90	
B0510MAA10-60P		60	14.50	15.50	17.70	16.40	
B0510MAA10-70P		70	17.00	18.00	20.20	18.90	
B0510MAA10-80P		80	19.50	20.50	22.70	21.40	
B0510MAA10-100P		100	24.50	25.50	27.70	26.40	

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN®	
DIM. x.x x.xx x.xxx GENERAL ANGLE: ±1.0°		TITLE: 0.5 Pitch双槽立式BTB公(单高1.0)					
		DWG. NO.: B0510MAA10-XP		CHECKED: MAX			
		PART NO.: B0510MAA10-XP		DRAWN: ELLA			
UNIT: mm		SCALE: none	SHEET: 2 of 2	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	