






ROHS




电路原理图



REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTES:
1.ELECTRICAL CHARACTERS:
1-1.RATING: DC 30V 0.5A;
1-2.CONTATCT RESISTANCE:≤30mΩ;
1-3.INSULATION RESISTANCE:≥100MΩ DC 500V;
1-4.WITHSTANDING VOLTAGE:AC 500V 1min;
1-5.LIFE:5,000 CYCLES;
2.MECHANICAL CHARACTERISTICS:
2-1.INSERTION&EXTRACTION FORCE:3~30N;
2-2.OPERATING TEMPERATURE:−30°C~+70°C;



6	插 针	1	H59(Y)黄铜棒 Ø=2.5mm	D. Cu/Sn
5	平 片	1	H62(Y)黄铜带 δ =0.4mm	D. Cu/Sn
4	后 盖	1	PA工程塑料	黑
3	弯 片	1	H62(Y)黄铜带 δ =0.35mm	D. Cu/Sn
2	簧 片	1	QSn6.5-0.1(Y)锡青铜带 δ =0.3mm	D. Sn/Sb
1	基 座	1	PA	黑
序号	名 称	数量	材 料	备 注
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司		
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD		
CHECK				
APPROVAL				
TOLERANCES ARE				
30-150	±0.35	ANGLE	TITLE	DC电源连接器D6.4C2.0(SMT)
10-30	±0.2		PART NO.	LAIL-DC30-D6.4C2.0G-T
5-10	±0.15		DWG.NO.	
0-5	±0.1			
			Projection	