


This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior concert&that no right is granted to disclose or to use any information in this document.

RoHS & HF
Compliant

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	INITIAL RELEASED	2026.08.11	JANUS

NOTE:

- 1.MATERIAL SPECIFICATION:
 - 1.HOUSING:PA9T(GP2300F), UL94 V-0.
 - 2.CONTACTS: COPPER ALLOY(C18150).
 - 3.MID PLATE: STAINLESS STEEL(SUS301).
 - 4.FRONT SHELL: STAINLESS STEEL(SUS304).
 - 5.EMI PLATE: STAINLESS STEEL(SUS304).
- 2.PLATING SPECIFICATION:
 - 2-1.CONTACTS:
Ni 50u" MIN. UNDER PLATED OVER ALL.
Au PLATED ON THE FUNCTIONAL AREA OF CONTACT.
(GOLD PLATING THICKNESS FOLLOW THE P/N)
PLATING SPECIFICATIONS OF THE SOLDER AREA FOLLOW THE P/N
 - 2-2.FRONT SHELL:
Ni 30u" MIN. UNDER PLATED OVER ALL.
 - 2-3.MID PLATE:
Ni 30u" MIN. UNDER PLATED OVER ALL.
Sn 80u"MIN. PLATED OVER ALL
 - 2-4.EMI PLATE:
CLEAR ONLY
- 3.MECHANICAL PERFORMANCE,
 - 3-1.INSERTION FORCE: 0.5~2.0kgf.
 - 3-2.REMOVAL FORCE: 0.8kgf~2.0kgf.
 - 3-3.DURABILITY: 10000 CYCLES.
- 4.ELECTRICAL PERFORMANCE,
 - 4-1.VOLTAGE RATING:48V DC/AC (RMS. MAX);
CURRENT RATING:5AMPS. FOR TOTAL VBUS/GND PINS;
1.25AMPS FOR CC PIN,0.25AMPS. FOR ALL OTHER CONTACT.
 - 4-2. LLCR:
VBUS & GND PINS AND OTHER PINS: 40mΩ/PIN MAX.
LLCR MAX. CHANGE OF ALL PINS: 10mΩ.
 - 4-3.INSULATION RESISTANCE: 100MΩ MIN
 - 4-4.DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.
5. ENVIRONMENTAL PERFORMANCE:
OPERATING TEMPERATURE: -40°C~+105°C.
- 6.IR REFLOW:
THE PEAK TEMPERATURE ON THE BOARD SHALL
BE MAINTAINED FOR 10 SECONDS AT 260°C.




TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10°	PART NO.	TITLE: TYPEC母座24PIN长7.9MM			
.XX ±0.20	.X* ± 8°	101047-211010	沉板1.0 (CH=0.58)			
.XXX ±0.10	.XX* ± 5°					
UNIT	mm	DESIGN: JANUS	DRAWG NO.			
MATERIAL	---	CHED: JANUS	C-101047			
FINISH	---	APPD: ARAY		SCALE	SHEET	REV.
				1:1	1/3	A

This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior consent&that no right is granted to disclose or to use any information in this document.


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	INITIAL RELEASED	2026.08.11	JANUS

RoHS & HF
Compliant



USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	TXp1	B11	RXp1
A3	TXn1	B10	RXn1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	RXn2	B3	TXn2
A11	RXp2	B2	TXp2
A12	GND	B1	GND



RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS 0.60MM;DEFAULT TOLERANCE:±0.05



P/N: 101047-211010

- CONTACT FUNCTIONAL AREA PLATED
01: Au G/F
- CONTACT SOLDER AREA PLATED
1: Au G/F
- PACKAGING
1: REEL PACKAGING

TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD			
X.X ±0.30	X.* ±10°	PART NO.	TITLE: TYPEC母座24PIN长7.9MM 沉板1.0 (CH=0.58)			
.XX ±0.20	.X.* ± 8°	101047-211010				
.XXX ±0.10	.XX.* ± 5°	DESIGN: JANUS	DRAWG NO. C-101047			
UNIT	mm	CHED: JANUS				
MATERIAL	---	APPD: ARAY		SCALE	SHEET	REV.
FINISH	---			1:1	2/3	A

This document is the property of Xinshengyue Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Xinshengyue Corporation without its prior concert&that no right is granted to disclose or to use any information in this document.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A	ECN NO.	INITIAL RELEASED	2026.08.11	JANUS



			REEL	CARTON	
		CONNECTOR (PCS)	1000	10000	
TOLERANCE		NAME(INTENDED USE) CUSTOMER DRAWING	XSUA® 深圳市新升跃精密电子有限公司 SHENZHEN XINSHENGYUE PRECISION ELECTRONICS CO., LTD		
X.X ±0.30	X.* ±10°	PART NO. 101047-211010			
.XX ±0.20	.X.* ± 8°	DESIGN: JANUS	TITLE: TYPEC母座24PIN长7.9MM 沉板1.0 (CH=0.58)		
.XXX ±0.10	.XX.* ± 5°				
UNIT	mm	DRAWG NO.	C-101047		
MATERIAL	---	CHED: JANUS			
FINISH	---	APPD: ARAY			
			SCALE	SHEET	REV.
			1:1	3/3	A