

A		B		C		D		E	
REV.		DESCRIPTION		ECN NO.		NAME		DATE	

1	Part No	CKT	A	B	C	D	E
	B0810MAA10-8P	8	2.40	3.45	5.10	4.20	4.00
	B0810MAA10-10P	10	3.20	4.25	5.90	5.00	
	B0810MAA10-12P	12	4.00	5.05	6.70	5.80	
	B0810MAA10-14P	14	4.80	5.85	7.50	6.60	
	B0810MAA10-16P	16	5.60	6.65	8.30	7.40	
	B0810MAA10-18P	18	6.40	7.45	9.10	8.20	
	B0810MAA10-20P	20	7.20	8.25	9.90	9.00	
B0810MAA10-22P	22	8.00	9.05	10.70	9.80		
2	B0810MAA10-24P	24	8.80	9.85	11.50	10.60	8.00
	B0810MAA10-26P	26	9.60	10.65	12.30	11.40	
	B0810MAA10-28P	28	10.40	11.45	13.10	12.20	
	B0810MAA10-30P	30	11.20	12.25	13.90	13.00	
	B0810MAA10-32P	32	12.00	13.05	14.70	13.80	
	B0810MAA10-34P	34	12.80	13.85	15.50	14.60	
	B0810MAA10-36P	36	13.6	14.65	16.30	15.40	
	B0810MAA10-38P	38	14.40	15.45	17.10	16.20	
3	B0810MAA10-40P	40	15.20	16.25	17.90	17.00	
	B0810MAA10-44P	44	16.80	17.85	19.50	18.60	
	B0810MAA10-50P	50	19.20	20.25	21.90	21.00	
	B0810MAA10-60P	60	23.20	24.25	25.90	25.00	
	B0810MAA10-70P	70	27.20	28.25	29.90	29.00	
	B0810MAA10-80P	80	31.20	32.25	33.90	33.00	
	B0810MAA10-100P	100	39.20	40.25	41.90	41.00	

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN®	
DIM. TOL.		TITLE: 0.8 Pitch 双槽 立式 BTB 公座(单高1.0)					
x.x ±0.50		DWG. NO.: B0810MAA10-XP					
x.xx ±0.20		PART NO.: B0810MAA10-XP					
x.xxx ±0.10		CHECKED: MAX					
GENERAL ANGLE: ±1.0°		DRAWN: ELLA				APPROVED: WILL	
		UNIT: mm					
		SCALE: none					
		SHEET: 2 of 2					
		DWG. SIZE: A4					
		LAYER: bxconn					