





ROHS



3-1.5x0.8



PCB HOLES(TOP VIEW)
GENERAL TOLERANCE:±0.1mm

NOTES:

1.ELECTRICAL CHARACTERS:

1-1.RATING: DC 30V 0.5A;

1-2.CONTATCT RESISTANCE:≤30mΩ;

1-3.INSULATION RESISTANCE:≥100MΩ DC 500V;


1-4.WITHSTANDING VOLTAGE:AC 500V 1min;

1-5.LIFE:5,000 CYCLES;

2.MECHANICAL CHARACTERISTICS:

2-1.INSERTION&EXTRACTION FORCE:3~30N;

2-2.OPERATING TEMPERATURE:−30°C~+70°C;



⑥	PIN		1	BRASS	CuSn PLATED
⑤	TERMINAL	3	1	BRASS t=0.3	CuSn PLATED
④	BREAK TERMINAL	2	1	BRASS t=0.3	CuSn PLATED
③	TIP SPRING	1	1	BRONZE t=0.3	SnSb PLATED
②	COVER		1	PBT	BLACK
①	HOUSING		1	PBT	BLACK
No.	PART NAME	TER'NO.	Q'TY	MATERIAL	REMARK

CUSTOMER DRAWING

SHENZHEN LAILIAN ELECTRONICS CO., LTD

DRAWING

CHECK

APPROVAL

TOLERANCES ARE

30-150

10-30

5-10

0-5

±0.35

±0.2

±0.15

±0.1

ANGLE

±3°

TITLE

DC电源连接器D4. 2C1. 3弯插

REV.

A

PART NO.

LAIL-DC30-D4. 2C1. 3G-W

UNITS

mm

DWG.NO.

Projection