

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

MATERIAL:

HOUSING: PBT,UL94V-0,BLACK.

MECHANICAL:

DURABILITY: 750 CYCLES MIN.

MATING FORCE: 2.2KG.F MAX.

RETENTION STRENGTH : 7.7KG.F BETWEEN JACK AND PLUG.

OPERATING TEMPERATURE: -40°C~+85°C.

STORAGE TEMPERATURE: -40°C~+85°C.

ALL CRITICAL DIMENSIONS WITH "*"

ELECTRICAL:

VOLTAGE: 125 VOLTS AC.

CURRENT RATING:1.5AMP

DIELECTRIC STRENGTH: 1000 VAC RMS 50HZ OR 60HZ.1MIN






INSULATION RESISTANCE: 500 MEGA OHMS MIN.INITIAL

AFTER 500V DC FOR 1 MINUTE

CONTACT RESISTANCE: SINGLE TERMINAL 30 MILLIOHMS MAX

INITIAL 50 MILLIOHMS MAX. AFTER

DURABILITY TEST.



CUSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING		TITLE		1X1 4P4C 全塑	REV. A
CHECKED		PART NO.		LAIL-RJ11-LED0-BN-02G-WC	UNITS mm
APPROVED		DWG. NO.			Projection
TOLERANCES ARE					
30-150	±0.35	ANGLE			
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				