

A		B		C		D		E	
REV.		DESCRIPTION		ECN NO.		NAME		DATE	

1								
	2	PIN NO	PIN	DIM A	DIM B	DIM C	DIM D	DIM E
		B0510MAA13-8P	8	1.50	2.50	4.70	3.40	4.00
		B0510MAA13-10P	10	2.00	3.00	5.20	3.90	
		B0510MAA13-12P	12	2.50	3.50	5.70	4.40	
		B0510MAA13-14P	14	3.00	4.00	6.20	4.90	
		B0510MAA13-16P	16	3.50	4.50	6.70	5.40	
		B0510MAA13-18P	18	4.00	5.00	7.20	5.90	
		B0510MAA13-20P	20	4.50	5.50	7.70	6.40	
		B0510MAA13-22P	22	5.00	6.00	8.20	6.90	
B0510MAA13-24P		24	5.50	6.50	8.70	7.40		
B0510MAA13-26P	26	6.00	7.00	9.20	7.90			
3	B0510MAA13-28P	28	6.50	7.50	9.70	8.40	8.00	
	B0510MAA13-30P	30	7.00	8.00	10.20	8.90		
	B0510MAA13-32P	32	7.50	8.50	10.70	9.40		
	B0510MAA13-34P	34	8.00	9.00	11.20	9.90		
	B0510MAA13-36P	36	8.50	9.50	11.70	10.40		
	B0510MAA13-38P	38	9.00	10.00	12.20	10.90		
	B0510MAA13-40P	40	9.50	10.50	12.70	11.40		
	B0510MAA13-44P	44	10.50	11.50	13.70	12.40		
	B0510MAA13-50P	50	12.00	13.00	15.20	13.90		
	B0510MAA13-60P	60	14.50	15.50	17.70	16.40		
4	B0510MAA13-70P	70	17.00	18.00	20.20	18.90	8.00	
	B0510MAA13-80P	80	19.50	20.50	22.70	21.40		
	B0510MAA13-100P	100	24.50	25.50	27.70	26.40		
5								