







技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围： $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压： 125V, AC 。
4. 接触电阻： $\leq 0.02\Omega$ 。
5. 绝缘电阻： $\geq 100\text{M}\Omega$

序号	品名	材质
①	0.5 Pitch B型单槽 立式BTB插座嵌芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch B型单槽 立式BTB插座端子	铜合金/表面点镀金

Part No	CKT	A	B	C	D
BX-BTB0.5-26HGB1-8PLT	2X4	1.50	2.60	4.10	3.60
BX-BTB0.5-26HGB1-10PLT	2X5	2.00	3.10	4.60	4.10
BX-BTB0.5-26HGB1-12PLT	2X6	2.50	3.60	5.10	4.60
BX-BTB0.5-26HGB1-14PLT	2X7	3.00	4.10	5.60	5.10
BX-BTB0.5-26HGB1-16PLT	2X8	3.50	4.60	6.10	5.60
BX-BTB0.5-26HGB1-18PLT	2X9	4.00	5.10	6.60	6.10
BX-BTB0.5-26HGB1-20PLT	2X10	4.50	5.60	7.10	6.60
BX-BTB0.5-26HGB1-22PLT	2X11	5.00	6.10	7.60	7.10
BX-BTB0.5-26HGB1-24PLT	2X12	5.50	6.60	8.10	7.60
BX-BTB0.5-26HGB1-26PLT	2X13	6.00	7.10	8.60	8.10
BX-BTB0.5-26HGB1-28PLT	2X14	6.50	7.60	9.10	8.60
BX-BTB0.5-26HGB1-30PLT	2X15	7.00	8.10	9.60	9.10
BX-BTB0.5-26HGB1-32PLT	2X16	7.50	8.60	10.10	9.60
BX-BTB0.5-26HGB1-34PLT	2X17	8.00	9.10	10.60	10.10
BX-BTB0.5-26HGB1-36PLT	2X18	8.50	9.60	11.10	10.60
BX-BTB0.5-26HGB1-38PLT	2X19	9.00	10.10	11.60	11.10
BX-BTB0.5-26HGB1-40PLT	2X20	9.50	10.60	12.10	11.60
BX-BTB0.5-26HGB1-44PLT	2X22	10.50	11.60	13.10	12.60
BX-BTB0.5-26HGB1-50PLT	2X25	12.00	13.10	14.60	14.10
BX-BTB0.5-26HGB1-60PLT	2X30	14.50	15.60	17.10	16.60
BX-BTB0.5-26HGB1-70PLT	2X35	17.00	18.10	19.60	19.10
BX-BTB0.5-26HGB1-80PLT	2X40	19.50	20.60	22.10	21.60

台高(H)	公座单高	母座单高	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-BTB0.5-26HGB1-XPLT		版本 REV.	A
3.0	2.2	2.2				X.: ±0.50	±1°	审核 CHECK	EVA			品名 TITLE	0.5 Pitch B型半槽立式BTB公座(单高2.6)无焊片镀金		页次 SHEET	1/1
3.5	2.2	2.7				X.X: ±0.20		核准 APPROVAL	JADE			客户料号 CUTM.NO.				
4.0	2.2	3.2				X.XX: ±0.10		单位 UNITS	MM	比例 SCALE	1:1					
5.0	2.6	4.4														
1	2	3		4	5	6		7	8	9						