






ROHS



TECHNICAL FEATURES

1. OPERATING TEMPERATURE: -25 TO 70°C
2. RATED ELECTRONEGATIVITY: DC 30V 1.0A
3. CONTACT RESISTANCE: ≤30 mΩ
4. INSULATION RESISTANCE: ≥100MΩ
5. WITHSTAND VOLTAGE: AC500V (50HZ) /Min
6. INSERTION AND EXTRACTION FORCE: 3-25N
7. LIFESPAN: 5,000 TIMES



6	REAR COVER	1PCS	PBT/PPA/PA46	BLACK
5	BASE SEAT	1PCS	PBT/PPA/PA46	BLACK
4	INSERT A NEEDLE	1PCS	IRON SHEET	Ni PLATING
3	BULLET PIECE	1PCS	MANGANESE STEEL	Sn PLATING
2	CURVED SHEET	1PCS	IRON SHEET	Sn PLATING
1	FLAT PLATE	1PCS	IRON SHEET	Sn PLATING
NO	NAME	Q'TY	MATERIALS	REMARKS

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE		TITLE		DC电源连接器D6. 3C2. 5弯插	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-DC30-D6. 3C2. 5G-W	UNITS	mm
10-30	±0.2					
5-10	±0.15		DWG.NO.	Projection		
0-5	±0.1					
		±3°				