





A	B	C



5	序号	品名	材质
	①	0.8 Pitch B型立式 BTB公座胶芯	LCP UL94 V-0, 颜色:本色
	②	0.8 Pitch B型立式 BTB公座端子	铜合金/表面点镀金
	③	0.8 Pitch B型立式 BTB公座吸盖	不锈钢

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$. 3. 额定电压: $100\text{V}, \text{AC}$.
4. 接触电阻: $\leq 0.05\Omega$. 5. 绝缘电阻: $\geq 500\text{M}\Omega$

Part No	CKT	A	B	C
B0810MBA67-20P	2*10	7.20	13.80	12.20
B0810MBA67-22P	2*11	8.00	14.60	13.00
B0810MBA67-24P	2*12	8.80	15.40	13.80
B0810MBA67-26P	2*13	9.60	16.20	14.60
B0810MBA67-28P	2*14	10.40	17.00	15.40
B0810MBA67-30P	2*15	11.20	17.80	16.20
B0810MBA67-32P	2*16	12.00	18.60	17.00
B0810MBA67-34P	2*17	12.80	19.40	17.80
B0810MBA67-36P	2*18	13.60	20.20	18.60
B0810MBA67-38P	2*19	14.40	21.00	19.40
B0810MBA67-40P	2*20	15.20	21.80	20.20
B0810MBA67-42P	2*21	16.00	22.60	21.00
B0810MBA67-44P	2*22	16.80	23.40	21.80
B0810MBA67-46P	2*23	17.60	24.20	22.60
B0810MBA67-48P	2*24	18.40	25.00	23.40
B0810MBA67-50P	2*25	19.20	25.80	24.20
.....	...	...	...	...
B0810MBA67-200P	2*100	79.20	85.80	84.20

A		B		C		D		E	
REV.		DESCRIPTION		ECN NO.		NAME		DATE	















1


2


3

4

5

公座 (PLUG) 母座 (SOCKET)				
				
				
				
				



GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD	
DIM.	TOL.	TITLE: 0.8 Pitch B型 立式 BTB 公座(单高6.7)	
x.x	±0.50	DWG. NO.: B0810MBA67-XP	
x.xx	±0.20	CHECKED: MAX	
x.xxx	±0.10	DRAWN: ELLA	
GENERAL ANGLE:		PART NO.: B0810MBA67-XP	
±1.0°		APPROVED: WILL	
		UNIT:	SCALE:
		mm	none
		SHEET:	DWG. SIZE:
		2 of 2	A4
		LAYER:	
		bxconn	

