




















A		B		C		D		E	
REV.		DESCRIPTION		ECN NO.		NAME		DATE	

1	公座 (PLUG) 母座 (SOCKET)					
						
						
						
2						
						

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		 		
DIM. TOL. x.x ±0.50 x.xx ±0.20 x.xxx ±0.10 GENERAL ANGLE: ±1.0°		TITLE: 0.8 Pitch B型 立式 BTB 母座(单高3.7)				
		DWG. NO.: B0810FBA37-XP				CHECKED: MAX
		PART NO.: B0810FBA37-XP				DRAWN: ELLA
UNIT: mm	SCALE: none	SHEET: 2 of 2	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	