







REV	LTR	DESCRIPTION	DATE	APPROVED
A0				



备注:
1.材质:
1.1 胶芯: LCP+30%G.F UL94V-0
1.2 端子: 黄铜, T=0.18mm: 镍底50U" MIN,
接触区域镀金 (AU 0.5u") 焊脚雾锡
1.3 外壳: 不锈钢, T=0.25mm: 表面镀镍50U" MIN
1.4 中夹片: 不锈钢, T=0.15mm:
2.主要特性:
2.1额定电流: 3.8A
2.2接触阻抗: 40mΩ MAX(初始值)
50mΩ MAX(测试后)
2.3绝缘阻抗: 100MΩ MIN
2.4耐压测试: 100V AC R.M.S.
2.6整体插入力: 5-20N 整体插入力: 5-20N (耐久后)
整体拔出力:8-20N 整体拔出力:6-20N (耐久后)
2.7耐久: 5000次
2.8耐高温: SMT 回流焊 (峰值260°±5'), 塑胶不能有起泡,
融胶等不良,变色,翘曲变形在公差范围以内;
2.9产品须做焊锡测试,粘锡面积达到95%以上;
3.0盐雾测试: 24H MIN
3.1工作温度: -30℃~+85℃



A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-		VBUS			GND
GND			VBUS		D-	D+	CC1	VBUS			GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1



东莞市文章济美电子有限公司					
TOLERANCES .X ±0.30 .XX ±0.20 .XXX ±0.10 ANGLES ±1.00°			TITLE: TYPE-C 母座 14PIN 立插 高15.0		
APPD.:			PART NO.: 5001-USB2100990-081-B		
DRAWING NO.:					
CHECK:	REV.:	SIZE:	UNIT:	SCALE:	SHEET:
DRAWN:	A/0	A4	MM	1:1	1/1