










项目 Mapx	设 变 内 容 Modification	日 期 Date	修改人 Draw	核 准 Approve



NO.	DIM A	DIM B	DIM C
1	10.5	6.25	0.60
2	10.0	5.75	0.80
3	9.30	5.05	1.00
4	8.80	4.55	1.20
5			1.40
6			1.60

- 备注:
- 1.1 材质:
 - 1.2 端子: C18140, T=0.12mm; 镀半金锡
 - 1.3 外壳: 不锈钢, T=0.30mm; 表面镀镍
 - 1.4 接地片: 不锈钢, T=0.10mm;
 - 1.5 卡片: 不锈钢, T=0.15mm;
 2. 主要特性:
 - 2.1 额定电流: 3.0A
 - 2.2 接触阻抗: 40mΩ MAX
 - 2.3 绝缘阻抗: 100MΩ MIN 250V DC
 - 2.4 耐压测试: 100V AC
 - 2.5 沾锡性: 温度250±5℃, 时间5±0.5s
 - 2.6 整体插入力: 2.0kgf MAX
整体拔出力: 0.8kgf MIN
 - 2.7 使用寿命: 10000次
 - 2.8 工作温度: -30℃~+80℃

RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

成品图 MANUFACTURE DWG		东莞市文章济美电子有限公司									
公差一览表 TOLERANCE UNLESS OTHERWISE		日期 DATE	单位 UNIT	MM	制图 DRAWING	DWG NO.	品名 NAME	5001-USB0039589-081-B			
.X±0.15	.X±5°	审核 CHECKED	比例 SCALE	1:1	设计 DESIGN	LIUFU	USB Type-C 180夹板式		版本 VER	AO	页数 SHEET
XXX±0.05	.XX±1°	核准 APPROVE	角法 VIEW	⊕ ⊖							012