





REV.	DESCRIPTION OF REVISIONS	APPR.	CHKD.	DRAW.	DATE
△	New Release			DING	2022/04/25




RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE±0.05

Mating Dimension(mm)				
Item	L	H	W	M
Coaxial Cable Assembly	2.65±0.1	1.2±0.1	2.15±0.1	0.4±0.1



- 1.Rated Voltage: 60 V AC .;
- 2.Contact Resistance:20mOHM Max.;
- 3.Dielectric Withstanding Voltage:200V AC For 1 Minute;
- 4.Insulation Resistance:1000M OHM Min.;
- 5.Frequency Range: DC up to 6GHz
VSWR: 1.3 max. at 0~3GHz;
VSWR: 1.4 max. at 3~6GHz;
- 6.Operating Temperature: -40℃ to +90℃
- 7.Durability: 30 cycles
- 8.REC Connector shall stand IR reflow twice
- 9.▼As the focus control size

IR前	0.08
IR后	0.10



ITEM	PART NAME	Q'TY	MATERIAL	FINISH
1	SHELL	1	COPPER ALLOY	Au plated over Ni
2	Housing	1	High Temp.Plastic	Black UL94V-0
3	CONTACT	1	COPPER ALLOY	Au plated over Ni

Unless otherwise specified, other tolerance are:

X	±0.35	X*	±5°
X.X	±0.25	X.X*	±4°
X.XX	±0.15	X.XX*	±3°
X.XXX	±0.10	X.XXX*	±2°

PROJ. UNIT MM SCALE 1:1

CUSTOMER DRAWING

MUP MUP INDUSTRIAL CO.,LTD.

NAME: **RF IV REC Connector H=0.60mm**

MODEL NO: **MUP-R4154-01**

TYPE: **H=0.60mm, SMT TYPE**

DRAWN DING 2022/04/25 DWG NO.: **DWG-R4154-01-01**

CHECKED

APPROVAL WANG 2022/04/25 SHEET 1/1 REVISION 1

