

REV.	DESCRIPTION OF REVISIONS	APPR.	CHEC.	DRAW.	DATE
△	New			huabo	2024/11/06

A

B

C

D

E

F

A



B

C

D

E

F



- NOTES:
- MATERIAL :
 - HOUSING: THERMOPLASTIC, HIGH TEMPERATURE, UL94 V-0, COLOR: BLACK.
 - CONTACT: COPPER ALLOY.
 - FITTING NAIL: COPPER ALLOY.
 - FINISH :
 - CONTACT
GOLD PLATING ON THE CONTACT AREA.
GOLD FLASH PLATING ON THE SOLDERING AREA.
50u". NICKEL UNDERPLATING OVERALL.
 - FITTING NAIL
50u". MATTE-TIN PLATING ON THE SOLDERING AREA.
50u". NICKEL UNDERPLATING OVERALL.



Unless otherwise specified, other tolerance are:			MUP MUP INDUSTRIAL CO.,LTD.		
X ±0.40	X* ±5°		NAME: M.2 NGFF Connector		
X.X ±0.30	X.X* ±4°		MODEL NO: MUP-M2006-02		
X.XX ±0.20	X.XX* ±3°		TYPE: H4.0 PH0.5mm&67Pin-E KEY		
X.XXX ±0.10	X.XXX* ±2°		PROJ.	UNIT	SCALE
			mm	mm	1:1
CUSTOMER DRAWING			DRAWN	huabo 2024/11/06	DWG NO.: DWG-M2006-02-01
			CHECKED	huabo 2024/11/06	SHEET 1/1
			APPROVAL	wang 2024/11/06	REVISION 1