

1、Material: Nylon 66 UL94-V0(2)
2、Color: Nature

Technical drawing of a mechanical part showing three views: front, top, and side. The dimensions are given in millimeters with tolerances.

- Front View:** Shows a rectangular block with a semi-circular cutout on the right side. The total height is 7.45 ± 0.3 mm.
- Top View:** Shows a rectangular block with a rectangular cutout on the right side. The total width is 6.2 ± 0.3 mm. The width of the cutout is 7.1 ± 0.3 mm.
- Side View:** Shows a rectangular block with a rectangular cutout on the right side. The total height is 9.45 ± 0.3 mm.

Technical drawings of the mechanical part showing top and side views with dimensions.

Top View Dimensions:

- Overall width: 11.4 ± 0.3
- Inner width: 6.2 ± 0.1

Side View Dimensions:

- Overall height: 9.45 ± 0.3
- Height of the central section: 7.1 ± 0.3

Technical drawing of a stepped profile. The overall width is 23.8 ± 0.3 . The width of the first step is 6.2 ± 0.1 . The drawing shows a series of steps and arches.

Figure 1. Bridge structure

The drawing shows two views of a bridge structure. The top view is a side elevation showing a bridge with three arches. The total length of the bridge is indicated as 36.2 ± 0.3 . The bottom view is a cross-section of the bridge, showing the profile of the arches and the bridge deck. The height of the bridge is indicated as 9.45 ± 0.3 , and the width of the bridge deck is indicated as 7.1 ± 0.3 .

			GENERAL TOLERANCE	制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK				
			X. X ± 0.30	批 准 APPROVAL	产品名称 TITLE	VL (6.20)线锁扣	版 本 REV.	A
1	初版发行		X. XX ± 0.20	比 例 SCALE	产品料号 PART NO.	HC-VL-NS-05	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	X. XXX ± 0.10	投 影 Projection	材 料 MATERIAL		页 次 SHEET	1/1
			Angle ± 3.0°					