







REV.	DESCRIPTION OF REVISIONS	APPR.	CHKD.	DRAW.	DATE
△	新开			Zoey	2010/11/04
△	Original Model T302-2			huabo	2023/11/17



TECHNICAL CHARACTERISTICS

1.General Characteristics

Durability:5,000 cycles min.

2.Electrical Characteristics

Contact resistance:Initial: 50mΩ Max.

After Test: 100mΩ Max.

Insulation resistance:>1000MΩ/500V DC

3.Solderability

IR reflow:250°C,5sec.Max

Manual soldering:370°C,3sec.Max

4.Environmental Characteristics

Operating temperature:-40°C~+85°C

Operating humidity:10%~+95%RH

ITEM	PART NAME	Q'TY	MATERIAL	FINISH
1	HOUSING	1	Hi-temp Thermoplastic	Black UL94V-0
2	DATA CONTACT	3	Copper Alloy	Contact area:1u"Au plated
3	LATCH	1	Brass	Tin plated over all
Unless otherwise specified, other tolerance are:			MUP ® MUP INDUSTRIAL CO.,LTD.	
NAME:			Battery Connector	
MODEL NO:			MUP-T3002-02	
TYPE :			H7.5 with post 3p	
PROJ.	UNIT	SCALE	DRAWN	DWG NO.:
mm	mm	1:1	Zoey Nov.04.2010	DWG-T3002-02-01
CUSTOMER DRAWING			CHECKED	SHEET
			Zoey Nov.04.2010	1/1
			APPROVAL	REVISION
			Wang Nov.04.2010	2