





PRODUCT NO:		DS806MPR-0092		
REV	DESCRIPTION	DWN	DATE	APPROVEN
A	FIRST ISSUE	W. cheng	2020/10/14	John kine
B				



SPECIFICATIONS:

IMPEDANCE: 50 ohms
FREQUENCY RANGE: 0~6GHZ
VSWR: 1.5MAX
WORKING VOLTAGE: 500V RMS@SEA LEVEL
INSULATION RESISTANCE: 5000 ohms min
TEMPERATURE RANGE: -65° C TO +165° C
RELATIVE TEMPERATURE: ≤95%(40° C±2° C)



RECOMMENDED PCB LAYOUT

1	BODY	BRASS	GOLD-1u"	1	NOTE:	TOIERANCE	UNLESS OTHERWISE SPECIFIED TOLERANCES IN INCHES ARE 0.5-8MM±0.20MM 8-30MM±0.40MM 30-120MM±0.50MM	DOSIN —HF CONNECTOR— DOSIN INDUSTRIAL(HK) CO., LTD 东莞市德索五金电子有限公司 Dongguan Dosin Hardware Electronics Co.,Ltd. Web:http://www.dosinconn.com dosin2005@dosin-china.com E-mail:dosin2005@163.com Tel: (0086) 769-81153906 Fax: (0086) 769-81875836			
2	INSULATOR	TEFLON	WHITE	1							
3	CONTACT PIN	BRASS	GOLD-3u"	1							
4											
5					DRAWN W. cheng	2020/10/14	VIEW	NAME: SMA ANGLE JACK CONNECTOR			
6											
7					CHECKED		UNIT	SIZE A PRODUCT NO: DS806MPR-0092 REV A			
8											
9					APPROVALS		SCALE	DATETIME 2020/10/14		CAD FILE H/companydrawings/BD	SHEET:1 OF 1
10											
NO	COMPONENT NUMBER	MATERIAL	FINISH	QTY							