















REV.	ECN NO OR DESCRIPTION	REVISED	DATE
A	PROPOSE ONLY	ERIC	2022.01.18
B	UPDATE DRAWING	ERIC	2022.11.30
C	UPDATE DRAWING	ERIC	2023.02.02



CAP ASSEMBLY AND MOUTING CONDITION(REF.)




UNLESS OTHERWISE SPECIFIED TOLERANCES		 深圳市精睿兴业科技有限公司 SHENZHEN KRCNN TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	Type.C 8PIN Vertical DIP TYPE CONN. RECEPTACLE		
X :±0.5	X :±2°	DWN	chenjun	PART NO. TCR59-61120802-02	
X.X :±0.30	X.X :±1°	CHKD	chenjun	SCALE:1:1	UNIT: mm 
X.XX :±0.20		APVD	Kevin.d	SIZE: A4	SHEET:10F1
X.XXX :±0.10		DRAW NO. C-DWG-TCR59-01			CUSTOMER COPY

品质管控等级要求		
符号	等级	产品管控要求
▼	重点要求	巡检, 定义检验频率
▽	特殊性要求	CPK>1.33
◎	全检要求	自动机检验



REV.	ECN NO OR DESCRIPTION	REVISED	DATE
A	PROPOSE ONLY	ERIC	2022.01.18
B	UPDATE DRAWING	ERIC	2022.11.30
C	UPDATE DRAWING	ERIC	2023.02.02



 焊盘区域
 产品轮廓

(SC 2:1)
RECOMMENDED PCB LAYOUT(THICKNESS:0.80MM)
PWB TOLERANCE: ±0.05

PIN ASSIGNMENTS:

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND				CC1	D+	D-					GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
			VBUS				CC2	VBUS			


⑤	CAP	1 PCS	LCP	COLOR: BLACK	
④	SHELL	1 PCS	SUS304-1/2H T=0.30	Ni 50u" MIN	
③	MID PLATE	1 PCS	SUS301-H T=0.15	Ni 50u" MIN	
②	CONTACT	1 PCS	C2680 T=0.20mm	Ni 50u" MIN. CONTACT AREA:3u"Au BRUSH PLATING SOLDER AREA:0.6u"MIN Au BRUSH PLATING	
①	HOUSING	1 PCS	PPA 5600-GF25	COLOR: BLACK	
	NO.	DESCRIPTION	QTY.	MATERIAL	FINISH

UNLESS OTHERWISE
SPECIFIED TOLERANCES



深圳市精睿兴业科技有限公司
SHENZHEN KRCONN TECHNOLOGY CO., LTD







DRAW NO. C-DWG-TCR59-01	CUSTOMER COPY
-------------------------	---------------





REV.	ECN NO OR DESCRIPTION	REVISED	DATE
A	PROPOSE ONLY	ERIC	2022.01.18
B	UPDATE DRAWING	ERIC	2022.11.30
C	UPDATE DRAWING	ERIC	2023.02.02

CONN. PART NO.	CONN. QTY./REEL	REEL QTY./CARTON	CONN. QTY./CARTON
TCR59-61120802-02	600	10	6000 PCS



UNLESS OTHERWISE SPECIFIED TOLERANCES		深圳市精睿兴业科技有限公司 SHENZHEN KRCONN TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE Type.C 8PIN Vertical DIP TYPE CONN. RECEPTACLE			
X :±0.5	X :±2°	DWN	chenjun	PART NO. TCR59-61120802-02	
X.X :±0.30	X.X :±1°	CHKD	chenjun	SCALE:1:1	UNIT: mm
X.XX :±0.20		APVD	Kevin.d	SIZE: A4	SHEET:10F1
X.XXX :±0.10		DRAW NO. C-DWG-TCR59-01		CUSTOMER COPY	