




D

PIN ASSIGNMENTS:

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	TX1+	TX1-	V _{bus}	CC1	D+	D-	SBU1	V _{bus}	RX2-	RX2+	GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND	RX1+	RX1-	V _{bus}	SBU2	D-	D+	CC2	V _{bus}	TX2-	TX2+	GND





SPECIFICATION:

- 1.ELECTRICAL CHARACTERISTICS:
- 1.1 CURRENT RATING: 1.5A/Pin MAX(A4,A9,B4,B9)
1.25A/Pin MAX(A1,A12,B1,B12),0.25A(OTHER PIN)
- 1.2 CONTACT RESISTANCE: 40 MILLIONHM MAX.
- 1.3 DIELECTRIC WITHSTANDING VOLTAGE: 100 VAC r.m.s
- 1.4 INSULATION RESISTNACE: 100 MEGOHMS MIN.
- 2.MECHANICAL CHARACTERISTICS
- 2.1 INSERTION FORCE: 5~20N
- 2.2 EXTRACTION FORCE: Initial:8~20N;Durability:6~20N(1000cycles);
- 2.3 DURABILITY:10,000CYCLES
- 3.ENVIRONMENTAL CHARACTERISTICS
- 3.1 TEMPERATURE RANGE: -40 °C ~ 85 °C
- 3.2. IR REFLOW:
- THE PEAK TEMPERATURE ON THE BOARD SHALL
BE MAINTAINED FOR 10 SECONDS AT 260°C.
- 4.PART NO.:

TC R 06-32 1 1 24 02-01

TC=TYPE C CONN
R=RECEPTACLE
Product Order
32=HEIGHT ON BOARD 3.2mm
1=BLACK HOUSING
1=WITH DUL POST
01= Servics NO.
02=3u" Au Plating On Contact Aera
Pin NO. 24=24Pin



RECOMMENDED PCB LAYOUT(THICKNESS:0.80MM)
PWB TOLERANCE: ±0.05

④	SHELL	STAINLESS STEEL	NI Plated	1PCS
③	CENTER PLATE	STAINLESS STEEL	NI Plated	1PCS
②	CONTACT	COPPER ALLOY	Au/NI Plated	2SET
①	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

UNLESS OTHERWISE
SPECIFIED TOLERANCES





深圳市精睿兴业科技有限公司
SHENZHEN KRCONN TECHNOLOGY CO., LTD




DECIMALS:	ANGLES:	TITLE	Type.C 24PIN Dull SMT CONN. RECPTACLE		
X :±0.5	X :±2°	DWN chenjun	PART NO. TCR06-32112402-01		
X.X :±0.30	X.X :±1°	CHKD chenjun	SCALE:1:1	UNIT: mm	
X.XX :±0.20		APVD Kevin.d	SIZE: A4	SHEET:1OF1	REV: A
X.XXX :±0.10		DRAW NO. C-DWG-TCR06-01		CUSTOMER COPY	



REV.	ECN NO OR DESCRIPTION	REVISED	DATE
A	PROPOSE ONLY	ERIC	2020.05.08



← PRODUCT PACKAGING DIRECTION
CUSTOMER TO USE DIRECTION →



CONN. PART NO.	CONN. QTY./REEL	REEL QTY./CARTON	CONN. QTY./CARTON
TCR06-32112402-01	800	10	8000 PCS

UNLESS OTHERWISE SPECIFIED TOLERANCES		深圳市精睿兴业科技有限公司 SHENZHEN KRCONN TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	Type.C 24PIN Dull SMT CONN. RECPTACLE		
X :±0.5	X :±2°	DWN	chenjun	PART NO.	TCR06-32112402-01
X.X :±0.30	X.X :±1°	CHKD	chenjun	SCALE:1:1	UNIT: mm
X.XX :±0.20		APVD	Kevin.d	SIZE: A4	SHEET:10F1
X.XXX :±0.10					REV: A
DRAW NO. C-DWG-TCR06-01				CUSTOMER COPY	