

Features

- Ultra low capacitance: 0.35pF
- typical Ultra low leakage: nA level
- Low operating voltage: 1 V
- Low clamping voltage
- 2-pin leadless package
- Complies with following standards:
 - IEC 61000-4-2 (ESD) immunity test
Air discharge: $\pm 15\text{kV}$
Contact discharge: $\pm 12\text{kV}$
 - IEC61000-4-5 (Lightning) 4A (8/20 μs)
- RoHS Compliant


Applications

- USB Ports
- SIM Ports
- Smart Phones
- Wireless Systems
- Set-top box and digital TV
- Digital video interface (DVI)
- Ethernet 10/100 Base T


Mechanical Characteristics

- Package: DFN0603
- Lead Finish: Lead Free
- UL Flammability Classification Rating 94V-0
- Quantity Per Reel: 10,000pcs
- Reel Size: 7 inch
- Device Marking: 1C

Dimensions DFN0603



Pin Configuration



Absolute Maximum Ratings (T_{amb}=25°C unless otherwise specified)


Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20 μs)	P _{pp}	25	W
ESD per IEC 61000-4-2 (Air)	V _{ESD}	± 15	kV
ESD per IEC 61000-4-2 (Contact)		± 12	
Operating Temperature Range	T _J	-55 to +125	°C
Storage Temperature Range	T _{STJ}	-55 to +125	°C

Electrical Characteristics (TA=25°C unless otherwise specified)





Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V_{RWM}				1	V
Breakdown Voltage	V_{BR}	$I_T = 1\text{mA}$	1.4			V
Reverse Leakage Current	I_R	$V_{RWM} = 1\text{V}$			0.5	μA
Clamping Voltage	V_C	$I_{PP} = 4\text{A}$ (8 x 20 μs pulse)			6	V
Junction Capacitance	C_J	$V_R = 0\text{V}$, $f = 1\text{MHz}$		0.35	0.5	pF

Electrical Parameters (TA=25°C unless otherwise specified)


- V_{RWM} Reverse Working Voltage Max.
 I_R Maximum Reverse Leakage Current @ V_{RWM}
 V_{BR} Reverse Breakdown Voltage
 I_{PP} Maximum Reverse Peak Pulse Current
 V_C Clamping Voltage @ I_{PP}




Typical Performance Characteristics (TA=25°C unless otherwise specified)



DFN0603 Package Outline Drawing



Suggested Land Pattern



* This Land Pattern is For Reference Purposes Only

NOTICE

Leiditech reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Leiditech does not assume any liability arising out of the application or use of any product described herein.

Shanghai Leiditech Electronic Technology Co., Ltd.

Email: sale1@leiditech.com

Tel : +86- 021 50828806

Fax : +86- 021 50477059