







技术指标(Technical Index):

- 1.工作温度(Temperature range): $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):250V DC/AC(rms).
- 3.额定电流(Rated current):3.0A AC,DC.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.耐压值(Dielectricwithstanding voltage):
800V AC/minute.
- 6.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	CKT	A	B
A-PHD2.0-L2-Y2P71	2*2	2.0	6.0
A-PHD2.0-L2-Y3P71	2*3	4.0	8.0
A-PHD2.0-L2-Y4P71	2*4	6.0	10.0
A-PHD2.0-L2-Y5P71	2*5	8.0	12.0
A-PHD2.0-L2-Y6P71	2*6	10.0	14.0
A-PHD2.0-L2-Y7P71	2*7	12.0	16.0
A-PHD2.0-L2-Y8P71	2*8	14.0	18.0
A-PHD2.0-L2-Y9P71	2*9	16.0	20.0
A-PHD2.0-L2-Y10P71	2*10	18.0	22.0
A-PHD2.0-L2-Y11P71	2*11	20.0	24.0
A-PHD2.0-L2-Y12P71	2*12	22.0	26.0
A-PHD2.0-L2-Y13P71	2*13	24.0	28.0
A-PHD2.0-L2-Y14P71	2*14	26.0	30.0
A-PHD2.0-L2-Y15P71	2*15	28.0	32.0
A-PHD2.0-L2-Y16P71	2*16	30.0	34.0
A-PHD2.0-L2-Y17P71	2*17	32.0	36.0
A-PHD2.0-L2-Y18P71	2*18	34.0	38.0
A-PHD2.0-L2-Y19P71	2*19	36.0	40.0
A-PHD2.0-L2-Y20P71	2*20	38.0	42.0

序号	品名	材质			
1	PHD2.0直针WTB胶芯	PA66加玻纤 UL94 V-0 米色			
2	PHD2.0直针WTB端子	铜合金/表面镀锡			
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO.		TITLE:	
X.X±0.20		A-PHD2.0-L2-YNP71		PHD2.0 双排直插WTB	
X.XX±0.10		DESIGN: Ethan		MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		 SCALE SHEET	
MATERILA	— — —	APPD: Ava			
FINISH	— — —			N:A	1/1