


General Characteristics



VCEO	IC	VCE(sat)	fT	Tjmax
40V	600mA	1.0V	300MHz	150℃



Features

- SOT363 Package
- Epoxy meets UL-94 V-0 flammability rating and halogen free
- Moisture Sensitivity Level 3
- High temperature soldering guaranteed 260℃/10seconds

at terminals



Package Marking and Ordering Information

Product ID	Package	Marking	Qty(PCS)
MMDT2222A	SOT-363	K1P	3000



Maximum Ratings & Thermal Characteristics (Ratings at 25℃ ambient temperature unless otherwise specified.)







Parameters	Symbol	Value	Unit
Collector-Base Voltage	VCBO	75	V
Collector-Emitter Voltage	VCEO	40	V
Emitter -Base Voltage	VEBO	6	V
Collector Current-Continuous	IC	600	mA
Collector Power Dissipation	PC	200	mW
Junction Temperature	Tj	150	℃
Storage Temperature	Tstg	-55-+150	℃

Electrical Characteristics (Ratings at 25°C ambient temperature unless otherwise specified).

	Symbols	Test Condition	Limits		Unit
			Min	Max	
Collector-base breakdown voltage	V(BR)CBO	IC=10uA, IE=0	75		V
Collector-emitter breakdown voltage	V(BR)CEO	IC=10mA, IB=0	40		V
Emitter-base breakdown voltage	V(BR)EBO	IE=10uA, IC=0	6		V
Collector cut-off current	ICBO	VCB=60V, IE=0		10	nA
Collector cut-off current	ICEX	VCE=60V, VEB(off)=3V		10	nA
Emitter cut-off current	IEBO	VEB=3V, IC=0		10	nA
DC current gain	hFE(1)*	VCE=10V, IC=0.1mA	35		
	hFE(2)*	VCE=10V, IC=1mA	50		
	hFE(3)*	VCE=10V, IC=10mA	75		
	hFE(4)*	VCE=10V, IC=150mA	100	300	
	hFE(5)*	VCE=10V, IC=500mA	40		
	hFE(6)*	VCE=1V, IC=150mA	35		
Collector-emitter saturation voltage	VCE(sat)*	IC=500mA, IB=50mA		1.00	V
		IC=150mA, IB=15mA		0.30	V
Base -emitter saturation voltage	VBE(sat)*	IC=500mA, IB=50mA		2.00	V
		IC=150mA, IB=15mA	0.6	1.20	V
Transition frequency	fT	VCE=20V, IC=20mA, f=100MHz	300		MHz
Output Capacitance	Cob	VCB=10V, IE=0, f=1MHz		8	pF
Input Capacitance	Cib	VEB=0.5V, IC=0, f=1MHz		25	pF
Noise Figure	NF	VCE=10V, IC=100uA, f=1KHz, Rs=1KΩ		4	dB
Delay time	td	VCC=30V, VBE(off)=-0.5V, IC=150mA,		10	Ns
Rise time	tr	IB1=15mA		25	Ns
Storage time	ts	VCC=30V, IC=150mA, IB1=IB2=15mA		225	Ns
Fall time	tf			60	ns


Typical characteristics






Package Information

Carrier Dimension(mm)




Dimensions are in millimeter

Pkg Type	A	B	C	d	E	F	P0	P	P1	W
SOT-363	2.25	2.55	1.20	Ø1.50	1.75	3.50	4.00	4.00	2.00	8.00



Reel Dimension(mm)




Reel Option	D	D1	D2	G	H	I	W1	W2
7" Dia	Φ178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30
Tolerance	±2	±1	±1	±1	±1	±1	±1	±1

Package Specifications


Package	Reel Size	Reel DIA. (mm)	Q'TY/Reel (Kpcs)	Box Size (mm)	QTY/Box (Kpcs)	Carton Size (mm)	Q'TY/Carton (Kpcs)
SOT363	7'	178	3	210*208*203	45	440*400*230	180

Recommended Soldering Profile for Rectifier Diodes (Pb Free)

a) Wave Soldering Profile



b) Reflow Soldering Profile (Pb Free Application), refer to IPC/JEDEC J-STD-020




Preheat/Soak Temperature Min (T _{smin}) Temperature Max (T _{smax}) Time (ts) from (T _{smin} to T _{smax})	50 °C 200 °C 60-120 seconds
Melting Point of Solder (Sn Ag Cu)	217°C
Ramp-up Rate to 217°C(Melting Point of Solder)	3°C/sec
Time at Temp.>217°C (Melting Point of Solder)	60~150 Sec
Peak Temperature	255±5°C
Time within 5°Cbelow Peak Temp.	20~40 Sec
Cooling Rate	6°C/sec (max)
Time from 25°C to Peak Temp.	8min (max)

c) Manual Soldering


When using an electric soldering iron for manual soldering, it is recommended that the temperature does not exceed 300°C and the soldering time is less than 10 seconds.

Package Mechanical Data



Symbol	Dimensions In Millimeters	
	Min	Max
A	0.900	1.100
A1	0.000	0.100
A2	0.900	1.000
b	0.150	0.350
c	0.100	0.150
D	2.000	2.200
E	1.150	1.350
E1	2.150	2.400
e	0.650 TYP	
e1	1.200	1.400
L	0.525 REF	
L1	0.260	0.460
θ	0°	8°

Suggested Pad Layout



Note:
1. Controlling dimension; in millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.

Disclaimer

The information presented in this document is for reference only. Yancheng **Xirun Semiconductor Co., Ltd** reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), **Xirun Semiconductor** or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.

This publication supersedes & replaces all information previously supplied. For additional information, please visit our website [http:// www.x-semi.cn](http://www.x-semi.cn) , or consult your nearest **Xirun Semiconductor's** sales office for further assistance.