





MK-12 D14 N-G020-A N A A

Horizontal
Circuit Type
12=1P2T
G-Switch P/N
Reset Type
N=None
Switch Height (mm)
G020=2.0 G030=3.0
Operating Force
A=160gf
Cover Type
N=None
Base Type
A=With Column


G-Switch Specification:

1. Operating temperature range: -40°C ~ +85°C
2. Rating: 0.1A, 12V DC
3. Insulation resistance: 100MΩ min, 100V DC
4. Dielectric strength: 250V AC for 1 min
5. Contact resistance: 100mΩ max.
6. Travel: 2.0±0.3mm
7. Switch lifetime: 10,000Cycles



RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05

5	COVER	SUS	
4	BUTTON	PA46	BLACK
3	CONTACT	C5210	Ag PLATING
2	TERMINAL	C5210	Ag PLATING
1	BASE	PA	BLACK
NO.	PART NAME	MATERIAL	REMARK



CIRCUIT DIAGRAM



SCALE: 1:1	UNIT: mm	Title: Horizontal Mini Slide Switch SMT 9.1×3.5×H2.0mm				 品赞科技 www.dg-switch.com	
SIZE: A4		Molde Code: MK-12D14N-G020-ANAA					
Unless otherwise General Tolerance:		DRAWN	CHECKED	APPROVED	DATE		
X	±0.40	Lai	Chen	Chen	2025.08.05	REV: A0	SHEET: 1/1
X,x	±0.30						
X,xx	±0.20						
X°	±5°						
X,x°	±3°						