



General Description

V_{CEO}	I_C	$V_{CE(sat)}$	f_T	T_{jMax}
25V	500mA	0.6V	150MHz	150°C

Features

- SOT-523 Package
- Epoxy meets UL-94 V-0 flammability rating and halogen free
- Moisture Sensitivity Level 3
- High temperature soldering guaranteed 260°C/10seconds
at terminals


Package Marking and Ordering Information

Product ID	Package	Marking	Qty(PCS)
S8050T	SOT-523	J3Y	3000

Absolute Maximum Ratings (Ta=25°C unless otherwise noted)



Parameter	Symbols	Value	Units
Collector-Base Voltage	VCBO	40	V
Collector-Emitter Voltage	VCEO	25	V
Emitter -Base Voltage	VEBO	5	V
Collector Current-Continuous	IC	500	mA
Collector Power Dissipation	PC	200	mW
Junction Temperature	Tj	150	°C
Storage Temperature	Tstg	-55-+150	°C
Thermal resistance From junction to ambient	R θ JA	625	°C/W







Electrical Characteristics(Ta=25°C unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Max.	Unit
Collector-base breakdown voltage	V(BR)CBO	IC=100uA, IE=0	40		V
Collector-emitter breakdown voltage	V(BR)CEO	IC=1mA, IB=0	25		V
Emitter-base breakdown voltage	V(BR)EBO	IE=100uA, IC=0	5		V
Collector cut-off current	ICEO	VCE=20V, IB=0		100	nA
Collector cut-off current	ICBO	VCB=40V, IE=0		100	nA
Emitter cut-off current	IEBO	VEB=5V, IC=0		100	nA
DC current gain	Hfe(1)	VCE=1V, IC=50mA	120	400	
	hFE(2)	VCE=1V, IC=500mA	50		
Collector-emitter saturation voltage	VCE(sat)	IC=500mA, IB=50mA		0.60	V
Base -emitter saturation voltage	VBE(sat)	IC=500mA, IB=50mA		1.20	V
Base -emitter voltage	VBE	VCE=1V, IC= 10mA		0.70	V
Transition frequency	fT	VCE=6V, IC=20mA, f=30MHz	150		MHz

CLASSIFICATION OF hFE


RANK	L	H	J
RANGE	120-200	200-350	300-400

Typical characteristics





Package Information

Carrier Dimension(mm)




Dimensions are in millimeter

Pkg Type	A	B	C	d	E	F	P0	P	P1	W
SOT-523	1.85	1.85	0.875	Ø1.50	1.75	3.50	4.00	4.00	2.00	8.00





Reel Dimension(mm)



Reel Option	D	D1	D2	G	H	I	W1	W2
7"Dia	Φ178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30
Tolerance	±2	±1	±1	±1	±1	±1	±1	±1

Package Specifications




Package	Reel Size	Reel DIA. (mm)	Q'TY/Reel (Kpcs)	Box Size (mm)	QTY/Box (Kpcs)	Carton Size (mm)	Q'TY/Carton (Kpcs)
SOT523	7'	178	3	210*208*203	45	440*400*230	180

Recommended Soldering Profile for Rectifier Diodes (Pb Free)
a) Wave Soldering Profile

b) Reflow Soldering Profile (Pb Free Application), refer to IPC/JEDEC J-STD-020



Preheat/Soak Temperature Min (Tsmin) Temperature Max (Tsmax) Time (ts) from (Tsmin to Tsmax)	50 °C 200 °C 60-120 seconds
Melting Point of Solder (Sn Ag Cu)	217°C
Ramp-up Rate to 217°C(Melting Point of Solder)	3°C/sec
Time at Temp.>217°C (Melting Point of Solder)	60~150 Sec
Peak Temperature	255±5°C
Time within 5°Cbelow Peak Temp.	20~40 Sec
Cooling Rate	6°C/sec (max)
Time from 25°C to Peak Temp.	8min (max)

c) Manual Soldering

When using an electric soldering iron for manual soldering, it is recommended that the temperature does not exceed 300°C and the soldering time is less than 10 seconds.

Package Mechanical Data


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.700	0.900	0.028	0.035
A1	0.000	0.100	0.000	0.004
A2	0.700	0.800	0.028	0.031
b1	0.150	0.250	0.006	0.010
b2	0.250	0.350	0.010	0.014
c	0.100	0.200	0.004	0.008
D	1.500	1.700	0.059	0.067
E	0.700	0.900	0.028	0.035
E1	1.450	1.750	0.057	0.069
e	0.500 TYP.		0.020 TYP.	
e1	0.900	1.100	0.035	0.043
L	0.400 REF.		0.016 REF.	
L1	0.260	0.460	0.010	0.018
θ	0°	8°	0°	8°

Suggested Pad Layout


Note:

1. Controlling dimension: in millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.

Disclaimer

The information presented in this document is for reference only. Yancheng **Xirun Semiconductor Co., Ltd** reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), **Xirun Semiconductor** or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.

This publication supersedes & replaces all information previously supplied. For additional information, please visit our website [http:// www.x-semi.cn](http://www.x-semi.cn) , or consult your nearest **Xirun Semiconductor's** sales office for further assistance.