



Features


- Maximum output current IOM: 0.1A
- Output voltage Vo: 15V
- Continuous total dissipation PD: 0.6W (Ta=25°C)
- Moisture Sensitivity Level 3


Package Marking and Ordering Information

Product ID	Package	Marking	Qty(PCS)
78L15	SOT-89	78L15	1000

Absolute Maximum Ratings (Ta=25°C unless otherwise noted)

Parameters	Symbol	Value	Unit
Input Voltage	Vi	30	V
Operating Junction Temperature Range	TOPR	-25-+125	°C
Storage Temperature Range	Tstg	-65-+150	°C
Thermal Resistance from Junction to Ambient	RθJA	166.7	°C/W



TYPICAL APPLICATION






Note: Bypass capacitors are recommended for optimum stability and transient response and should be located as close as possible to the regulators.


Electrical Characteristics(Ta=25°C unless otherwise noted)

(Vi=10V, Io=40mA, Ci=0.33uF, Co=0.1uF, unless otherwise specified).

Parameter	Symbol	Test Conditions		Limits			Unit
				Min.	Typ.	Max.	
Output Voltage	Vo		25°C	14.4	15	15.6	V
		17.5V≤Vi≤30V, Io=1mA~40mA	0-125°C	14.25	15	15.75	V
		Vi=23V, Io=1mA~70mA		14.25	15	15.75	V
Load Regulation	ΔVo	Io=1mA~100mA, Vi=23V	25°C		25	150	mV
		Io=1mA~40mA, Vi=23V	25°C		15	75	mV
Line Regulation	ΔVo	17.5V≤Vi≤30V, Io=40mA	0-125°C		65	300	mV
		19V≤Vi≤30V, Io=40mA	25°C		58	250	mV
Quiescent Current	Iq		25°C		4.6	6.5	mA
Quiescent Current Change	ΔIq	19V≤Vi≤30V, Io=40mA	0-125°C			1.5	mA
	ΔIq	1mA≤Vi≤40mA, Vi=23V	0-125°C			0.1	mA
Output Noise Voltage	VN	10Hz≤f≤100KHz	25°C		82		uV/Vo
Ripple Rejection	RR	18.5V≤Vi≤28.5V, f=120Hz	25°C	34	39		dB
Dropout Voltage	Vd		25°C		1.7		V



Typical characteristics




Package Information
Carrier Dimension(mm)


Dimensions are in millimeter

Pkg Type	A	B	C	d	E	F	P0	P	P1	W
SOT-89-3L	4.85	4.45	1.85	Ø1.50	1.75	5.50	4.00	8.00	2.00	12.00
(Tolerance)	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	+0.3/-0.1


Reel Dimension(mm)



Reel Option	D	D1	D2	G	H	I	W1	W2
7"Dia	Φ180.00	60.00	R32.00	R86.50	R30.00	Φ13.00	13.20	16.50
Tolerance	±2	±1	±1	±1	±1	±1	±1	±1

Package Specifications


Package	Reel Size	Reel DIA. (mm)	Q'TY/Reel (Kpcs)	Box Size (mm)	QTY/Box (Kpcs)	Carton Size (mm)	Q'TY/Carton (Kpcs)
SOT89	7'	178	1	210*208*203	10	440*400*230	40

Recommended Soldering Profile for Rectifier Diodes (Pb Free)

a) Wave Soldering Profile



b) Reflow Soldering Profile (Pb Free Application), refer to IPC/JEDEC J-STD-020




Preheat/Soak Temperature Min (T _{smin}) Temperature Max (T _{smax}) Time (ts) from (T _{smin} to T _{smax})	50 °C 200 °C 60-120 seconds
Melting Point of Solder (Sn Ag Cu)	217°C
Ramp-up Rate to 217°C(Melting Point of Solder)	3°C/sec
Time at Temp.>217°C (Melting Point of Solder)	60~150 Sec
Peak Temperature	255±5°C
Time within 5°Cbelow Peak Temp.	20~40 Sec
Cooling Rate	6°C/sec (max)
Time from 25°C to Peak Temp.	8min (max)

c) Manual Soldering


When using an electric soldering iron for manual soldering, it is recommended that the temperature does not exceed 300°C and the soldering time is less than 10 seconds.

Package Mechanical Data



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.400	1.600	0.055	0.063
b	0.320	0.520	0.013	0.020
b1	0.400	0.580	0.016	0.023
c	0.350	0.440	0.014	0.017
D	4.400	4.600	0.173	0.181
D1	1.550 REF.		0.061 REF.	
E	2.300	2.600	0.091	0.102
E1	3.940	4.250	0.155	0.167
e	1.500 TYP.		0.060 TYP.	
e1	3.000 TYP.		0.118 TYP.	
L	0.900	1.200	0.035	0.047

Suggested Pad Layout



Note:

1. Controlling dimension: in millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.

Disclaimer

The information presented in this document is for reference only. Yancheng **Xirun Semiconductor Co., Ltd** reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), **Xirun Semiconductor** or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.

This publication supersedes & replaces all information previously supplied. For additional information, please visit our website [http:// www.x-semi.cn](http://www.x-semi.cn) , or consult your nearest **Xirun Semiconductor's** sales office for further assistance.