



RoHS

REV	ECN NO.	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2026.07.27









P.C.B Hole Layout

SPECIFICATIONS
1. Current rating: 2A
2. Temperature range: -40°C ~ +105°C
3. Insulation resistance: 1000MΩ Min.
4. Withstanding voltage: 500V AC/ minute.
5. Contact resistance: 20mΩ Max.

Material:
Insulator Material:PA6T (UL 94V-0)
Contact Material:Brass
Plating:Matte Tin or gold plated over Nickel
Mate with XFCN PZ200 Double Row series

Ordering Code:

PM200VS-11-XX-H43-A
1 2 3

1.序列号
2.Pin位数: 02-40P
3.A=第一脚朝上
4.默认=管装
R=加盖卷装

No.of PIN/ROW	Dimension A	B
02	2.00	4.40
03	4.00	6.40
04	6.00	8.40
05	8.00	10.40
06	10.00	12.40
07	12.00	14.40
08	14.00	16.40
09	16.00	18.40
10	18.00	20.40
11	20.00	22.40
12	22.00	24.40
13	24.00	26.40
14	26.00	28.40
15	28.00	30.40
16	30.00	32.40
17	32.00	34.40
18	34.00	36.40
19	36.00	38.40
20	38.00	40.40
21	40.00	42.40
22	42.00	44.40
23	44.00	46.40
24	46.00	48.40
25	48.00	50.40
26	50.00	52.40
27	52.00	54.40
28	54.00	56.40
29	56.00	58.40
30	58.00	60.40
31	60.00	62.40
32	62.00	64.40
33	64.00	66.40
34	66.00	68.40
35	68.00	70.40
36	70.00	72.40
37	72.00	74.40
38	74.00	76.40
39	76.00	78.40
40	78.00	80.40

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

PART NO: PM200VS-11-XX-H43-A

TITLE: 2.00mm Female Header Connectors

XFCN兴飞连接器

0769-82001899

www.xfconn.com

DWG NO: /

APPD	Chen ZhiQiang			
CHKD	Liu Wei	VIEW		
DRAW	Chen HongJiang	SCALE	SHEET	REV
DATE	2026.07.27	NONE	1/1	A1

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED,COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN