






2~3P结构样式

4P 结构样式



#### 技术指标:


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 工作温度:  $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$ 。
3. 额定电压: 250V DC/AC(rms)。
4. 额定电流: 3.0A AC, DC。
5. 接触电阻:  $\leq 20\text{m}\Omega$ 。
6. 耐压值: 800V AC/minute。
7. 绝缘电阻:  $\geq 1000\text{M}\Omega$ 。



SUGGESTED PCB LAYOUT  
(COMPONENT SIDE)

| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|------|--------|
|      |         |             |      |        |
|      |         |             |      |        |

| Part No            | Pin  | A    | B    | C    |
|--------------------|------|------|------|------|
| A-PHB2.0-W2-Y2P71  | 2*2  | 2.0  | 6.0  | 3.2  |
| A-PHB2.0-W2-Y3P71  | 2*3  | 4.0  | 8.0  | 3.2  |
| A-PHB2.0-W2-Y4P71  | 2*4  | 6.0  | 10.0 | 3.0  |
| A-PHB2.0-W2-Y5P71  | 2*5  | 8.0  | 12.0 | 5.0  |
| A-PHB2.0-W2-Y6P71  | 2*6  | 10.0 | 14.0 | 7.0  |
| A-PHB2.0-W2-Y7P71  | 2*7  | 12.0 | 16.0 | 9.0  |
| A-PHB2.0-W2-Y8P71  | 2*8  | 14.0 | 18.0 | 11.0 |
| A-PHB2.0-W2-Y9P71  | 2*9  | 16.0 | 20.0 | 13.0 |
| A-PHB2.0-W2-Y10P71 | 2*10 | 18.0 | 22.0 | 15.0 |
| A-PHB2.0-W2-Y11P71 | 2*11 | 20.0 | 24.0 | 17.0 |
| A-PHB2.0-W2-Y12P71 | 2*12 | 22.0 | 26.0 | 19.0 |
| A-PHB2.0-W2-Y13P71 | 2*13 | 24.0 | 28.0 | 21.0 |
| A-PHB2.0-W2-Y14P71 | 2*14 | 26.0 | 30.0 | 23.0 |
| A-PHB2.0-W2-Y15P71 | 2*15 | 28.0 | 32.0 | 25.0 |
| A-PHB2.0-W2-Y16P71 | 2*16 | 30.0 | 34.0 | 27.0 |
| A-PHB2.0-W2-Y17P71 | 2*17 | 32.0 | 36.0 | 29.0 |
| A-PHB2.0-W2-Y18P71 | 2*18 | 34.0 | 38.0 | 31.0 |
| A-PHB2.0-W2-Y19P71 | 2*19 | 36.0 | 40.0 | 33.0 |
| A-PHB2.0-W2-Y20P71 | 2*20 | 38.0 | 42.0 | 35.0 |
| A-PHB2.0-W2-Y21P71 | 2*21 | 40.0 | 44.0 | 37.0 |
| A-PHB2.0-W2-Y22P71 | 2*22 | 42.0 | 46.0 | 39.0 |

| 序号        | 品名                   | 材质                                                                                                                                                                  |                                                                                       |                      |       |
|-----------|----------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|----------------------|-------|
| 1         | 2.0—A型双排卧式DIP型WTB胶芯  | PA46 UL94V—0 白色                                                                                                                                                     |                                                                                       |                      |       |
| 2         | 2.0—A型双排卧式DIP型WTB长端子 | 铜合金／表面镀锡                                                                                                                                                            |                                                                                       |                      |       |
| 3         | 2.0—A型双排卧式DIP型WTB短端子 | 铜合金／表面镀锡                                                                                                                                                            |                                                                                       |                      |       |
| TOLERANCE |                      | <div>深圳聚兴泰电子科技有限公司<br/>Shenzhen Juxingtai Electronic Technology Co., Ltd</div> |                                                                                       |                      |       |
| .X±0.20   | ±2°                  |                                                                                                                                                                     | PART NO.                                                                              | TITLE:               |       |
| .XX±0.10  |                      |                                                                                                                                                                     | A—PHB2.0—W2—YNP71                                                                     | 2.00 Pitch A型双排卧式WTB |       |
| .XXX±0.05 |                      |                                                                                                                                                                     | DESIGN: Ethan                                                                         | MANUFACTURE DWG      |       |
| UNITS     | mm                   |                                                                                                                                                                     | CHED: Olvia                                                                           |                      |       |
| MATERILA  | — — —                | CHED: Olvia                                                                                                                                                         |                                                                                       |                      |       |
| FINISH    | — — —                | APPD: Ava                                                                                                                                                           |  | SCALE                | SHEET |
|           |                      |                                                                                                                                                                     | N:A                                                                                   | 1/1                  |       |