









技术指标:


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 工作温度: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$ 。
3. 额定电压: 250V DC/AC(rms)。
4. 额定电流: 3.0A AC, DC。
5. 接触电阻: $\leq 20\text{m}\Omega$ 。
6. 耐压值: 800V AC/minute。
7. 绝缘电阻: $\geq 1000\text{M}\Omega$ 。



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B	C
A-PHB2.0-L2-Y2P71	2*2	2.0	6.0	3.2
A-PHB2.0-L2-Y3P71	2*3	4.0	8.0	3.2
A-PHB2.0-L2-Y4P71	2*4	6.0	10.0	3.0
A-PHB2.0-L2-Y5P71	2*5	8.0	12.0	5.0
A-PHB2.0-L2-Y6P71	2*6	10.0	14.0	7.0
A-PHB2.0-L2-Y7P71	2*7	12.0	16.0	9.0
A-PHB2.0-L2-Y8P71	2*8	14.0	18.0	11.0
A-PHB2.0-L2-Y9P71	2*9	16.0	20.0	13.0
A-PHB2.0-L2-Y10P71	2*10	18.0	22.0	15.0
A-PHB2.0-L2-Y11P71	2*11	20.0	24.0	17.0
A-PHB2.0-L2-Y12P71	2*12	22.0	26.0	19.0
A-PHB2.0-L2-Y13P71	2*13	24.0	28.0	21.0
A-PHB2.0-L2-Y14P71	2*14	26.0	30.0	23.0
A-PHB2.0-L2-Y15P71	2*15	28.0	32.0	25.0
A-PHB2.0-L2-Y16P71	2*16	30.0	34.0	27.0
A-PHB2.0-L2-Y17P71	2*17	32.0	36.0	29.0
A-PHB2.0-L2-Y18P71	2*18	34.0	38.0	31.0
A-PHB2.0-L2-Y19P71	2*19	36.0	40.0	33.0
A-PHB2.0-L2-Y20P71	2*20	38.0	42.0	35.0
A-PHB2.0-L2-Y21P71	2*21	40.0	44.0	37.0
A-PHB2.0-L2-Y22P71	2*22	42.0	46.0	39.0

序号	品名	材质		
1	2.0A型双排立式WTB胶芯	PA46 UL94V-0 白色		
2	2.0F型卧式2代WTB端子	铜合金/表面镀锡		
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
.X±0.20	±2°	PART NO.	TITLE:	
.XX±0.10		A-PHB2.0-L2-YNP71	2.00 Pitch A型双排直插WTB	
.XXX±0.05		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		
MATERILA	— — —	APPD: Ava		SCALE
FINISH	— — —		N:A	1/1