







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

技术指标:


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$ (含通电时的温度上升值).
3. 额定电压: 30V, AC/DC.
4. 接触电阻: 初期 $\leq 0.02\Omega$, 环境试验后 $\leq 0.04\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$ min.
6. 额定电流: 0.5A, AC/DC
(使用AWG#28~#32, O.D 0.6mm MAX).
7. 耐压: AC 200V/1分钟.

材质:

1. LCP 本色



Part No	CKT	A	B	C	D
C-0.8-1-Y2P41	2	0.80	1.80	2.30	4.30
C-0.8-1-Y3P41	3	1.60	2.60	3.10	5.10
C-0.8-1-Y4P41	4	2.40	3.40	3.90	5.90
C-0.8-1-Y5P41	5	3.20	4.20	4.70	6.70
C-0.8-1-Y6P41	6	4.00	5.00	5.50	7.50
C-0.8-1-Y7P41	7	4.80	5.80	6.30	8.30
C-0.8-1-Y8P41	8	5.60	6.60	7.10	9.10
C-0.8-1-Y9P41	9	6.40	7.40	7.90	9.90
C-0.8-1-Y10P41	10	7.20	8.20	8.70	10.70
C-0.8-1-Y11P41	11	8.00	9.00	9.50	11.50
C-0.8-1-Y12P41	12	8.80	9.80	10.30	12.30
C-0.8-1-Y13P41	13	9.60	10.60	11.10	13.10
C-0.8-1-Y14P41	14	10.40	11.40	11.90	13.90
C-0.8-1-Y15P41	15	11.20	12.20	12.70	14.70
C-0.8-1-Y16P41	16	12.00	13.00	13.50	15.50
C-0.8-1-Y17P41	17	12.80	13.80	14.30	16.30
C-0.8-1-Y18P41	18	13.60	14.60	15.10	17.10
C-0.8-1-Y19P41	19	14.40	15.40	15.90	17.90
C-0.8-1-Y20P41	20	15.20	16.20	16.70	18.70
C-0.8-1-Y21P41	21	16.00	17.00	17.50	19.50
C-0.8-1-Y22P41	22	16.80	17.80	18.30	20.30
C-0.8-1-Y23P41	23	17.60	18.60	19.10	21.10
C-0.8-1-Y24P41	24	18.40	19.40	19.90	21.90
C-0.8-1-Y25P41	25	19.20	20.20	20.70	22.70

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	±1°	PART NO. C-0.8-1-YNP41	TITLE: 0.8 Pitch C型 WTB公头胶壳		
X.X±0.20					
X.XX±0.10					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/1