




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




技术指标(Technical Index):

- 1.工作温度(Temperature range): $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$.
- 2.适用线规(Apply to gauge):AWG#28~#22
- 3.额定电压(Rated voltage):250V DC/AC(rms).
- 4.额定电流(Rated current):3.0A AC,DC.
- 5.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 6.耐压值(Dielectricwithstanding voltage):800V AC/minute.
- 7.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.




Part No	Pin	A	B
D-PHD2.0-L2-M2P42	2*2	2.00	6.00
D-PHD2.0-L2-M3P42	2*3	4.00	8.00
D-PHD2.0-L2-M4P42	2*4	6.00	10.00
D-PHD2.0-L2-M5P42	2*5	8.00	12.00
D-PHD2.0-L2-M6P42	2*6	10.00	14.00
D-PHD2.0-L2-M7P42	2*7	12.00	16.00
D-PHD2.0-L2-M8P42	2*8	14.00	18.00
D-PHD2.0-L2-M9P42	2*9	16.00	20.00
D-PHD2.0-L2-M10P42	2*10	18.00	22.00
D-PHD2.0-L2-M11P42	2*11	20.00	24.00
D-PHD2.0-L2-M12P42	2*12	22.00	26.00
D-PHD2.0-L2-M13P42	2*13	24.00	28.00
D-PHD2.0-L2-M14P42	2*14	26.00	30.00
D-PHD2.0-L2-M15P42	2*15	28.00	32.00
D-PHD2.0-L2-M16P42	2*16	30.00	34.00
D-PHD2.0-L2-M18P42	2*18	34.00	38.00
D-PHD2.0-L2-M20P42	2*20	38.00	42.00





SUGGESTED PCB LAYOUT
(COMPONENT SIDE)
适用线路板(厚度:1.6mm)

1	PHD立贴WTB胶芯	LCP UL94V-0 米色
2	PHD立贴(连续)端子	铜合金/表面镀锡
3	PHD2.0立贴WTB吸盖	LCP UL94V-0 米色
序号	名称	材质



2P 结构样式



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.25	X.*±3°	PART NO.	TITLE:		
.XX±0.12	X.X°±0.5°	D-PHD2.0-L2-MNP42	2.0 Pitch D型双排立贴		
.XXX±0.05		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/1
FINISH	— — —				