

NPN Plastic-Encapsulate Transistors






General Description

V_{CEO}	I_C	$V_{CE(sat)}$	f_T	T_{jMax}
160V	0.6A	0.2V@ $I_C=50mA$	100MHz	150°C

Features

- SOT-89 Package
- Epoxy meets UL-94 V-0 flammability rating and halogen free
- Moisture Sensitivity Level 3
- High temperature soldering guaranteed 260°C/10seconds at terminals



Package Marking and Ordering Information

Product ID	Package	Marking	Qty(PCS)
CXT5551	SOT-89	1G6	1000



Absolute Maximum Ratings (Ta=25°C unless otherwise noted)






Parameter	Symbols	Rating	Units
Collector-Base Voltage	VCBO	180	V
Collector-Emitter Voltage	VCEO	160	V
Emitter -Base Voltage	VEBO	6	V
Collector Current-Continuous	I_C	0.6	A
Collector Power Dissipation	PC	0.5	W
Thermal Resistance, Junction to Ambient Air	RθJA	250	° C/W
Operating and Storage Temperature Range	TJ,TSTG	-55-+150	°C

Electrical Characteristics(Ta=25°C unless otherwise noted)

Parameter	Symbol	Conditions	Limits		
			Min.	Max.	Unit
Collector-base breakdown voltage	V(BR)CBO	IC=100uA, IE=0	180		V
Collector-emitter breakdown voltage	V(BR)CEO	IC=1mA, IB=0	160		V
Emitter-base breakdown voltage	V(BR)EBO	IE=10uA, IC=0	6		V
Collector cut-off current	ICBO	VCB=120V, IE=0		50	nA
Collector cut-off current	IEBO	VEB=4V, IC=0		50	nA
DC current gain	hFE(1)	VCE=5V, IC=1mA	80		
	hFE(2)	VCE=5V, IC=10mA	100	300	
	hFE(3)	VCE=5V, IC=50mA	30		
Collector-emitter saturation voltage	VCE(sat)	IC=10mA, IB=1mA		0.15	V
		IC=50mA, IB=5mA		0.2	V
Base -emitter voltage	VBE(sat)	IC=10mA, IB=1mA		1	V
		IC=50mA, IB=5mA		1	
Transition frequency	fT	VCE=10V, IC=10mA, f=100MHz	100		MHz
Output capacitance	Cob	VCB=10V, IE=0, f=1MHz		6	pF
Noise figure	NF	VCE=5V, IC=0.2mA, f=10Hz to 15.7KHz, Rs=10Ω		8	dB


Typical characteristics



NPN Plastic-Encapsulate Transistors



Package Information

Carrier Dimension(mm)




Dimensions are in millimeter

Pkg Type	A	B	C	d	E	F	P0	P	P1	W
SOT-89-3L	4.85	4.45	1.85	Ø1.50	1.75	5.50	4.00	8.00	2.00	12.00
(Tolerance)	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	+0.3/-0.1



Reel Dimension(mm)




Reel Option	D	D1	D2	G	H	I	W1	W2
7"Dia	Φ180.00	60.00	R32.00	R86.50	R30.00	Φ13.00	13.20	16.50
Tolerance	±2	±1	±1	±1	±1	±1	±1	±1

Package Specifications


Package	Reel Size	Reel DIA. (mm)	Q'TY/Reel (Kpcs)	Box Size (mm)	QTY/Box (Kpcs)	Carton Size (mm)	Q'TY/Carton (Kpcs)
SOT89	7'	178	1	210*208*203	10	440*400*230	40

Recommended Soldering Profile for Rectifier Diodes (Pb Free)

a) Wave Soldering Profile



b) Reflow Soldering Profile (Pb Free Application), refer to IPC/JEDEC J-STD-020




Preheat/Soak Temperature Min (Tsmin) Temperature Max (Tsmax) Time (ts) from (Tsmin to Tsmax)	50 °C 200 °C 60-120 seconds
Melting Point of Solder (Sn Ag Cu)	217°C
Ramp-up Rate to 217°C(Melting Point of Solder)	3°C/sec
Time at Temp.>217°C (Melting Point of Solder)	60~150 Sec
Peak Temperature	255±5°C
Time within 5°Cbelow Peak Temp.	20~40 Sec
Cooling Rate	6°C/sec (max)
Time from 25°C to Peak Temp.	8min (max)

c) Manual Soldering


When using an electric soldering iron for manual soldering, it is recommended that the temperature does not exceed 300°C and the soldering time is less than 10 seconds.

Package Mechanical Data



Symbol	Dimensions in Millimeters		Dimensions in Inches	
	Min	Max	Min	Max
A	1.400	1.600	0.055	0.063
b	0.320	0.520	0.013	0.020
b1	0.400	0.580	0.016	0.023
c	0.350	0.440	0.014	0.017
D	4.400	4.600	0.173	0.181
D1	1.550 REF.		0.061 REF.	
E	2.300	2.600	0.091	0.102
E1	3.940	4.250	0.155	0.167
e	1.500 TYP.		0.060 TYP.	
e1	3.000 TYP.		0.118 TYP.	
L	0.900	1.200	0.035	0.047

Suggested Pad Layout



Note:

1. Controlling dimension: in millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.

Disclaimer

The information presented in this document is for reference only. Yancheng **Xirun Semiconductor Co., Ltd** reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), **Xirun Semiconductor** or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.

This publication supersedes & replaces all information previously supplied. For additional information, please visit our website [http:// www.x-semi.cn](http://www.x-semi.cn) , or consult your nearest **Xirun Semiconductor's** sales office for further assistance.