

1		2		3		4		5		6		7		8	
芯 数		2 芯		3 芯		4 芯		5 芯		6 芯		7 芯		8 芯	
E	接触对排列分布 从针的方向看														
	额定电流/电压	7A-125V		7A-125V		7A-125V		7A-125V		5A-125V		5A-125V		5A-125V	
	工作电压 (AC.V) 分钟	200		200		200		200		200		200		200	
	耐电压 (AC.V) 1分钟	1500		1500		1500		1500		1500		1500		1500	
	绝缘阻抗 (MΩ) DV500V	1500		1500		1500		1500		1500		1500		1500	
	接触阻抗 (MΩ) DC1A	5		5		5		5		5		5		5	
D	焊杯口径 φ (mm)	1.6		1.6		1.6		1.2		0.9		0.9		0.9	
	接触对孔径 φ (mm)	2.45		2.45		2.45		2		1.15		1.15		1.15	
C	1). 未注公差±0.5 2) 接触方式; 螺母连接 3) 接插次数: 500次 4) 温度范围; -20℃~+85℃ 6) 接触体材料; 铜 (镀金/银)														
	序号 图 号 名 称 数量 材 料 处 理 1 压线块 1 锌合金 镀镍 2 压线块螺丝 2 钢 3 母头外壳 1 锌合金 镀镍 4 胶芯固定螺丝 1 钢 5 连接螺母 1 锌合金 镀镍 6 铜针 铜 镀金/镀银 7 绝缘件 1 电木 GX16-F-**-A-A Material Attribute: Standard Mold Number: A085 Pin Layout: 02-10PIN Port: F-Female / H-Male Series: GX16														
B	SAMZO COMPONENTS Electronic switch and connector manufacturer GENERAL TOLERANCE ≥0~2< ±0.15 ≥2~5< ±0.25 ≥0~2< ±0.15 ≥5 ±0.35 FIRST VIEW SCALE 1:1 UNIT mm The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM														
	REV ECN NO DESCRIPTION DESIGN APPROVAL DATE DESIGN WANGGUIFA 2013.02.12 A1 NEW Replace frame 2013.02.12 CHECKED ZHENGUILAN 2013.02.12 APPROVED LILIANJIANG 2013.02.14 SVHC/ROHS TITLE: GX16母端 PART NO: GX16-F-XX-A-A DWG NO: GX16-P085 MODEL NO: GX16F0601 NAME: Aviation connector														
1		2		3		4		5		6		7		8	

