










RECOMMENDED PCB PATTERN LAYOUT GENERAL TOLERANCE: ±0.05



Specifications:
 Current Rating: 1A Max
 Contact Resistance: 50 milliohms MAX
 Dielectric Withstanding Voltage: 100V AC AT Sea Level
 Insulation Resistance: 100 MEGA ohms MIN
 Housing:
 Temperature Thermoplastics, LCP UL 94V-0
 Contact:
 Copper Alloy T=0.20mm Plated Gold in Mating Area;
 Tin On Solder Tails
 Shell: Brass T=0.25mm Nickel/Plating

Total mating force: 3.57 Kgf MAX.
 Total unmating force: 1.0 Kgf Min. 0.81~2.05 Kgf Min. after 10000 insertion/extraction cycles
 Temperature range: -30° C~80° C


Ordering Code:

MUFM19 - X - L - X - X - X
 ① ② ③ ④ ⑤ ⑥

- ① Series No:
- ② Shell Material:
 B: Brass
 I: Iron
 S: stainless steel
- ③ Insulator Material:
 P: PBT+30%GF
 L: LCP
- ④ Contact Material:
 B: Brass
 P: phosphor copper
- ⑤ Contact Plating
 G0: Gold flash
 G1: 3u" Gold
 G2: 5u" Gold
 G3: 10u" Gold
 G4: 15u" Gold
 G5: 30u" Gold
- ⑥ Packing
 A: Tray
 B: Bag
 C: Tube
 D: Tape & Reel

Unless Otherwise specified tolerance
 X. XX: ±0.35 X. XX: ±0.20
 X. X: ±0.25 X. XXX: ±0.15

SCALE: As Shown UNIT: mm
 DRAW: Lv Xun Hua DATE: 01/06/2019
 CHECK: BobYang DATE: 01/06/2019



Antenk ANTENK ELECTRONICS CO., LTD
 Http://www.antenk.com
 E-mail: sales@antenk.com

TITLE: MICRO USB AB EJECTOR TYPE
 RECEPTACLE 4SHELL DIP (8.35mm+4.45mm)

DRAWING NO: MUFM19-BLBG0D

PRODUCT NO: MUFM19-BLBG0D

REV	DESCRIPTION	DATE
1		
2		
3		
4		
5		