




NOTES:

备注

- 1.Brass or purple copper,tin-plating
黄铜, 镀锡
- 2.Wire screw hole M5 (M4, M6)
压线螺孔M5 (M4, M6) 可定制
- 3.Current Rating: 90A
额定电流: 90A
4. There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
6. 扭矩: 2.03Nm

Ordering Information

HC		-	*	*	*	-	*****	-	*	*****	-	07
Type	Thickness	Screw	Welding	Series	Product No.	Material						
插针 (插针)	0.5mm	螺孔 (螺孔)	焊点 (焊点)	100mmx20mm	产品序号	紫铜 (紫铜)						
插针 (插针)	0.5mm	螺孔 (螺孔)	焊点 (焊点)	100mmx20mm	产品序号	紫铜 (紫铜)						
插针 (插针)	0.5mm	螺孔 (螺孔)	焊点 (焊点)	100mmx20mm	产品序号	紫铜 (紫铜)						
插针 (插针)	0.5mm	螺孔 (螺孔)	焊点 (焊点)	100mmx20mm	产品序号	紫铜 (紫铜)						
插针 (插针)	0.5mm	螺孔 (螺孔)	焊点 (焊点)	100mmx20mm	产品序号	紫铜 (紫铜)						
插针 (插针)	0.5mm	螺孔 (螺孔)	焊点 (焊点)	100mmx20mm	产品序号	紫铜 (紫铜)						



			GENERAL TOLERANCE	制图	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD						
			DIM TOL	审核		产品名称	PCB 焊接端子 厚度1.5 平贴片	版本	A			
			5 or more ±0.35	批准		TITLE	抽牙 M5 30x10x3mm	REV.				
			2~5 ±0.25	比例		产品料号	HC-M1550-3010-S734-07	单位	mm			
			0~2 ±0.15	SCALE		PART NO.		UNITS				
序号	变更内容	日期	Angle ±3.0°	投影		材料		页次	1/1			
No.	MODIFY CONTENT	MODIFY DATE				MATERIAL		SHEET				