







7		8	
REV.	REVISION DESCRIPTION	DATE	APPD

PCB Layout (Tolerance ± 0.05)


Circuits	Product name	Diensmion		Circuits	Product name	Diensmion	
		A	B			A	B
2	PHG-2AS	2.00	8.00	10	PHG-10AS	18.00	24.00
3	PHG-3AS	4.00	10.00	11	PHG-11AS	20.00	26.00
4	PHG-4AS	6.00	12.00	12	PHG-12AS	22.00	28.00
5	PHG-5AS	8.00	14.00	13	PHG-13AS	24.00	30.00
6	PHG-6AS	10.00	16.00	14	PHG-14AS	26.00	32.00
7	PHG-7AS	12.00	18.00	15	PHG-15AS	28.00	34.00
8	PHG-8AS	14.00	20.00	~	~	~	~
9	PHG-9AS	16.00	22.00	20	PHG-20AS	38.00	44.00

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: PHG-XAS		TITLE: 2.00 mm Pitch Wire To Board Wafer	
.XX: ± 0.15	.X° : ± 2.0°				
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:25.11.01	PART NO:	
FINISH: _____		CHKD: Wu Hui	DATE:25.11.01		
DRAWING NO:		APPD:Ren An De	DATE:25.11.01	SCALE: N/A	PAGE: 1/1
				UNITS: mm	REV.: A




REV.	REVISION DESCRIPTION	DATE


Key Location




2 Circuit




3 Circuit



4 Circuit



5 Circuit




6-20 Circuit

NOTES:

1. Rated voltage: 250V AC/DC
2. Rated current: 2.5A AC/DC (AWG#22 max)
3. Contact resistance: $\leq 20 \text{ m}\Omega$
4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
5. Withstand voltage: 1000V AC/minute
6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
7. Material :PA66 UL94V-0

Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
2	PHG-2Y	2.00	7.30	12	PHG-12Y	22.00	27.30
3	PHG-3Y	4.00	9.30	13	PHG-13Y	24.00	29.30
4	PHG-4Y	6.00	11.30	14	PHG-14Y	26.00	31.30
5	PHG-5Y	8.00	13.30	15	PHG-15Y	28.00	33.30
6	PHG-6Y	10.00	15.30	16	PHG-16Y	30.00	35.30
7	PHG-7Y	12.00	17.30	17	PHG-17Y	32.00	37.30
8	PHG-8Y	14.00	19.30	18	PHG-18Y	34.00	39.30
9	PHG-9Y	16.00	21.30	19	PHG-19Y	36.00	41.30
10	PHG-10Y	18.00	23.30	20	PHG-20Y	38.00	43.30
11	PHG-11Y	20.00	25.30	~	~	~	~

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: PHG-XY	TITLE: 2.00 mm Pitch Housing
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Chen Quan Long	DATE: 26/04/16
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE: 26/04/16
FINISH:		APPD: Ren An De	DATE: 26/04/16
DRAWING NO:			



REV.	REVISION DESCRIPTION	DATE	

- NOTES:
- 1.Rated voltage: 250V AC.DC
 - 2.Rated current: 2.5A AC DC(AWG#22 max)
 - 3.Contact resistance: ≤20 mΩ
 - 4.Insulation resistance: ≥1000 MΩ
 - 5.Withstand voltage: 1000V AC/minute
 - 6.Ambient temprature:-40℃~+105℃
 - 7.Material :PA66 UL94V-0

Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	C			A	C
2	PHG-2S	2.00	7.30	12	PHG-12S	22.00	27.30
3	PHG-3S	4.00	9.30	13	PHG-13S	24.00	29.30
4	PHG-4S	6.00	11.30	14	PHG-14S	26.00	31.30
5	PHG-5S	8.00	13.30	15	PHG-15S	28.00	33.30
6	PHG-6S	10.00	15.30	16	PHG-16S	30.00	35.30
7	PHG-7S	12.00	17.30	17	PHG-17S	32.00	37.30
8	PHG-8S	14.00	19.30	18	PHG-18S	34.00	39.30
9	PHG-9S	16.00	21.30	19	PHG-19S	36.00	41.30
10	PHG-10S	18.00	23.30	20	PHG-20S	38.00	43.30
11	PHG-11S	20.00	25.30	~	~	~	~

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: PHG-XS		TITLE: 2.00 mm Pitch	
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long		DATE:26/04/16	
.XXX: ± 0.01	.XX° : ± 1.0°	DATE:26/04/16		PART NO:	
FINISH:		CHKD: Wu Hui		SCALE: N/A	
DRAWING NO:		DATE:26/04/16		PAGE: 1/1	
		APPD: Ren An De		UNITS: mm	
				REV.: A	

