





HSF



ROHS



PCB LAYOUT



SPECIFICATION

Current Rating: 1Amp
 Insulation Resistance: 1000M ohms min
 Contact Resistance: 20M ohms max
 Dielectric Withstanding: AC500V
 Operating Temperature: -65°C to +125°C
 Contact Material: Brass
 Insulator Material: PA6T, UL 94V-0 Black

Ordering Code:

PHCU04 - ① - ② - ③ - ④ - ⑤ - ⑥ - ⑦

① Series No:

② No. of Contacts
01 To 50

③ Contact Plating:

G0: Gold flash S0: Selective
 G1: 3u" Gold S1: Selective 3u"
 G2: 5u" Gold S2: Selective 5u"
 G3: 10u" Gold S3: Selective 10u"
 G4: 15u" Gold S4: Selective 15u"
 G5: 30u" Gold S5: Selective 30u"

SN: Tin

④ Connector Type
D: Single

⑤ Pin Length:

A: 0260=2.60mm

D: 0200=2.00mm

W: 0500=5.00mm

Please mark the desired length in the A/D/W

⑥ Insulator Material

B: PA6T

C: LCP

E: PA9T

⑦ Packing:

A: Tray

B: Bag

T: Tube

U: Tube+CAP

R: Tape&Reel


W: Tape&Reel+CAP

Standard IE P/N : PHCU04-07-G0-D-0265-0505-0397-B-B

A	D	W
2.6	5.5	3.97

Optional

Unless Otherwise specified tolerance
 X. ±0.35 X.XX: ±0.20
 X.X: ±0.25 X.XXX: ±0.15

SCALE:
As ShownUNIT:
mmDRAW
YG ZHONGDATE
01/05/2016CHECK
BobYangDATE
01/05/2016

3rd ANGLE PROJECTION



ANTENK ELECTRONICS CO., LTD

Http://www.antenk.com

E-mail:sales@antenk.com

TITLE:

1.27mm Pin Header Single Row Angle C Type

DRAWING NO: PHCU04-07-G0-D-0265-0505-0397-B-B

PRODUCT NO: PHCU04-07-G0-D-0265-0505-0397-B-B

REV	DESCRIPTION	DATE
1	Increase packing method and material	2016/10/25