





HSF



RoHS



PCB LAYOUT

SPECIFICATION

Current Rating: 1.5 Amp
Insulation Resistance: 1000M ohms min
Contact Resistance: 20M ohms max
Dielectric Withstanding: AC500V
Operating Temperature: -65 °C to +125 °C
Contact Material: Brass
Insulator Material: PA6T,UL 94V-0 Black

Ordering Code:

PHDS06 - $\frac{X}{1}$ - $\frac{X}{2}$ - $\frac{D}{3}$ - $\frac{A-C-B}{4}$ - $\frac{X}{5}$ - $\frac{X}{6}$ - $\frac{X}{7}$ - $\frac{X}{8}$

① Series No:

② No. of Contacts
02 To 80

③ Contact Plating:

G0: Gold flash S0: Selective
G1: 3U" Gold S1: Selective 3u"
G2: 5u" Gold S2: Selective 5u"
G3: 10u" Gold S3: Selective 10u"
G4: 15u" Gold S4: Selective 15u"
G5: 30u" Gold S5: Selective 30u"
SN: Tin

④ Connector Type
D: Dual

⑤ Pin Length:

A: 0400=4.00mm
C: 0588=5.88mm
B: 0280=2.80mm

Please mark the desired length in the A/C/B

⑥ Insulator Material

A: PBT
B: PA6T
C: LCP
D: PA46
E: PA9T

⑦ Packing:

A: Tray
B: Bag
T: Tube
U: Tube+CAP
R: Tape&Reel
W: Tape&Reel+CAP

⑧ Plastic High


H1: 1.5mm
H2: 2.0mm

Standard IE P/N :

PHDS06-28G0D-0400-0588-0280-BBH1

A	C	B	Unless Otherwise specified tolerance	
0.40	0.58	0.28	X. ±0.35	X.XX: ±0.20
			X.X: ±0.25	X.XXX: ±0.15
Optional			SCALE: As Shown	UNIT: mm

DRAW
YG ZHONG
DATE
01/05/2016
CHECK
BobYang
DATE
01/05/2016



Antenk ANTENK ELECTRONICS CO., LTD
Http://www.antenk.com
E-mail:sales@antenk.com

TITLE: 2.00mm Pin Header DualRow Double
Plastic Straight Type

DRAWING NO: PHDS06-28G0D-0400-0588-0280-BBH1

PRODUCT NO: PHDS06-28G0D-0400-0588-0280-BBH1

Increase packing method and material

2016/10/25

DESCRIPTION

DATE

REV

1

2

3

4

5

6

7

8