



PCB 参考安装方式

NOTES:

备注

- 1.Brass or purple copper,tin-plating
黄铜, 镀锡
- 2.Wire screw hole M4 (M3,M5)
压线螺孔M4 (M3,M5)可定制
- 3.Current Rating: 70A
额定电流:70A
- 4.There shall be no defects such as
pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
6. 扭矩: 1.47 Nm

Ordering Information

HC - * ** * * - ***** - D *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	IP	Product No.	Material
10=Pull Teeth (牙)	10=0.8mm	3=6 (螺牙)	4=0 (焊脚)	0808x0.8mm	S=ST	产品序号	默认=Cooper (黄铜)
12=Pull Nut (螺母)	12=1.2mm	3=6 (螺牙)	4=0 (焊脚)	1620=16x20mm	IP=Lat D=IP		IP=Lat (黄铜)
10=Pull Gasket (橡胶片)	10=2.0mm 22=2.5mm 30=3.0mm	3=6 (螺牙)	4=0 (焊脚)				IP=Lat (黄铜)



工程专用章			GENERAL TOLERANCE	制 图 DRAWING	07		 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK						
			5 or more ±0.35	批 准 APPROVAL	产品名称 TITLE	PCB 焊接端子 厚度1.2 插板 抽牙 M4 4焊脚 9.1x9.1x8.7mm	版 本 REV.	A		
1	初版发行		2~5 ±0.25	比 例 SCALE	产品料号 PART NO.	HC-M1244-0909-D535-07	单 位 UNITS	mm		
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	0~2 ±0.15	投 影 Projection	 材料 MATERIAL		页 次 SHEET	1/1		
			Angle ±3.0°							