

Specification Sheet for Approved

Customer Name:	
Customer Part No.:	
Ceaiya Part No:	MTF0630-1R5MT
Spec No:	TF0630

【For Customer Approval Only】

If you Approval, Please Stamp

【RoHS Compliant Parts】

Approved By	Checked By	Prepared By
李庆辉	苏高峰	劳水花

Shenzhen Ceaiya Electronics Co., Ltd.

地址 1: 深圳市龙华区观湖街道鹭湖社区观盛二路 5 号捷顺科技中心 B706

地址 2: 东莞清溪镇青滨东路 105 号力合紫荆智能制造中心 10 栋

Http://www.szceaiya.com

Tel: 0769-89333213

【Version of Changed Record】

Rev.	Effective Date	Changed Contents	Change Reasons	Approved By
A0	2026-08-11	New release	/	Li qing hui

Specification Sheet for SMD Power Inductor

1. Scope

This specification applies to the MTF0630 Series of wire wound SMD power inductor.

2. Product Description and Identification (Part Number)

1) Description:

MTF0630 series of Wire wound SMD power inductor.

2) Product Identification (Part Number)

MTF 0630 - 1R5 M T
① ② ③ ④ ⑤

①	Type
MTF	Molded Power Inductor

②	External Dimensions(L×W×H) 【mm】
0630	6.6×6.4×3.1

④	Inductance Tolerance
N	± 30%
M	± 20%

③	Nominal Inductance
Example	Example
R68	0.68uH
1R0	1.0uH
100	10uH

⑤	Packing
T	Tape Carrier Package

3. Electrical Characteristics

Please refer to Item 5.


1) Operating temperature range (individual chip without packing): -40℃ ~ +125℃ (Including Self-heating) .

2) Storage temperature range (packaging conditions): -10℃ ~ +40℃ and RH 70% (Max.).

4. Shape and Dimensions (Unit:mm)

Dimensions and recommended PCB pattern for reflow soldering, please see Fig4-1 and Table4-1

Shape and Dimensions:



Recommended pad:




Fig4-1.

Table 4-1.

A	B	C	D	E	F	a	b	c
6.6±0.3	6.4±0.3	3.0Max	6.6Typ.	1.9±0.3	2.5Typ.	2.3 Ref	2.3 Ref	7.0Ref

Specification Sheet for SMD Power Inductor

5. Electrical Characteristics

Part Number	Inductance	DC Resistance		Saturation Current		Heat Rating Current		Marking
	1MHz/1V	Max.	Typ.	Max.	Typ.	Max.	Typ.	
Units	uH	mΩ	mΩ	A		A		
Symbol	L	DCR		Isat		Irms		
MTF0630-1R5MT	1.5±20%	8.20	6.90	18.0	22.0	10.5	14.5	1R5

Note:※1: Rated current: Isat(max.)or Irms(max.),whichever is smaller;

※2: Isat: DC current at which the inductance drops approximate 30% from its value without current;



※3: Irms: DC current that causes the temperature rise ($\Delta T = 40^{\circ}\text{C}$) from 25°C ambient.

The part temperature (ambient + temp. rise) should not exceed 125°C under worst case operating conditions. Circuit design, component placement, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.


※4:Absolute maximum voltage:DC 50V

6. Structure

The structure of MTF0630 product.





NO.	Components	Material
①	Core	Soft magnetic Metal
②	Wire	Polyurethane system enameled copper wire
③-1	Electrodes	Inside Cu
③-2		Ni+Sn Plating Chemicals



Δf: Clearance between terminal and the surface of plate must be 0.15mm max when coil is placed on a flat plate.

Specification Sheet for SMD Power Inductor

6. Reliability Test

Items	Requirements	Test Methods and Remarks
7.1 Bonding Strength	Chip coil shall not be damaged.	It shall be soldered on the substrate. Applying Force(F): 10N Hold Duration: 5s 
7.2 Vibration	No visible mechanical damage. Inductance change: Within $\pm 10\%$ 	1) Solder the inductor to the testing jig (glass epoxy board) using eutectic solder. 2) The inductor shall be subjected to a simple harmonic motion having total amplitude of 1.5mm, the frequency being varied uniformly between the approximate limits of 10 and 55Hz. 3) The frequency range from 10 to 55Hz and return to 10Hz shall be traversed in approximately 1 minute. this motion shall be applied for a period of 2 hours in each 3 mutually perpendicular directions (total of 6 hours).
7.3 Solderability	The wetting area of the electrode shall be at least 90% covered with new solder coating.	Flux: Ethanol solution of rosin, 25(wt)% Solder : Sn-3.0Ag-0.5Cu Pre-Heating: 150 $\pm$ 10 $^{\circ}$ C / 60 to 90s Solder Temperature: 245 $\pm$ 5 $^{\circ}$ C Immersion Time: 3 s
7.4 Resistance to Soldering Heat	Appearance: No damage Inductance Change : within $\pm 10\%$	Reflow soldering method Flux: Ethanol solution of rosin, 25(wt)% Solder: Sn-3.0Ag-0.5Cu Pre-Heating: 150 to 180 $^{\circ}$ C / 60 to 120s Solder Temperature: 230 $^{\circ}$ C min. / 20 to 40s Peak Temperature: 250 $\pm$ 5/-0 $^{\circ}$ C Reflow times: 2 times max Test board shall be 0.8 mm thick. Base material shall be glass epoxy resin. Then measured after exposure Standard atmospheric conditions for 1~2h.
7.5 Heat Resistance	Appearance: No damage Inductance Change : within $\pm 10\%$	Temperature: 125 $\pm$ 2 $^{\circ}$ C Time: 500h ($\pm$ 12h) Then measured after exposure Standard atmospheric conditions for 1~2h.
7.6 Cold Resistance	Appearance: No damage Inductance Change : within $\pm 10\%$	Temperature: -40 $\pm$ 2 $^{\circ}$ C Time: 500h ($\pm$ 12h) Then measured after exposure Standard atmospheric conditions for 1~2h.

Specification Sheet for SMD Power Inductor


7. Reliability Test

Items	Requirements	Test Methods and Remarks
7.7 Humidity	Appearance: No damage Inductance Change : within $\pm 10\%$	Temperature: $40 \pm 2^\circ\text{C}$ Humidity: 90 to 95%(RH) Time: 500h ($\pm 12\text{h}$) Then measured after
7.8 Temperature Cycle		1 cycle: 1 step: $-40 \pm 2^\circ\text{C}$ / $30 \pm 3\text{m}$ 2 step: Ordinary temp. / 3m max. 3 step: $+125 \pm 2^\circ\text{C}$ / $30 \pm 3\text{m}$ 4 step: Ordinary temp. / 3m max. Total of 100 cycles Then measured after exposure Standard atmospheric conditions for 1~2h.

8. Iron soldering

The following conditions must be strictly followed when using a soldering iron.


Pre-heating	150°C 1 minute
Tip temperature	350°C max
Soldering iron output	30w max
End of soldering iron	$\phi 1\text{mm}$ max
Soldering time	3 seconds max



Specification Sheet for SMD Power Inductor


9.Packaging and Marking:

9-1.Carrier Tape Dimensions:




ITEM	W	A0	B0	K0	P	F	E	D0	P2	T
DIM	16.00	6.2	6.4	3.35	12.0	7.5	1.75	1.5	12.00	0.50
TOLE	±0.2	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.2	±0.1	±0.05

9-2.Taping Dimensions:



9-3.Reel Dimensions:



Type	A	B	C
16mm	16.5±1	2.0±1	100±1

9-4. Packaging Quantity:

1.0KPCS/ Reel