

Glass Passivated Junction Transient Voltage Suppressor

P_{PP} 30000W


V_{RWM} 28V~360V

FEATURES

- ◆ Plastic package has Underwriters Laboratory
- ◆ Flammability Classification 94V-0
- ◆ Glass passivated junction
- ◆ 30000W Peak Pulse Power
- ◆ capability on 10/1000 μ s waveform
- ◆ Excellent clamping capability
- ◆ Repetition rate (duty cycle): 0.05%
- ◆ Low incremental surge resistance
- ◆ Fast response time: typically less than 1.0 ps from 0 volts to BV
- ◆ Typical Id less than 1 μ A above 10V
- ◆ High temperature soldering guaranteed: 265°C/10 seconds/.375", (9.5mm) lead length, 5lbs., (2.3kg) tension

MECHANICAL DATA

- ◆ Case: Molded plastic over glass passivated junction Terminals: Plated Axial leads, solderable perMIL-STD-750, Method 2026
- ◆ Polarity: Color band denoted positive end (cathode) except Bipolar
- ◆ Mounting Position: Any Weight: 0.07 ounce, 2.1 gram



Maximum Ratings and Characteristics @ 25°C Ambient Temperature (unless otherwise noted)

Parameter	Symbol	Value	Unit
Peak Pulse Power Dissipation on 10/1000 μ s Waveform (Note 1)	P_{PPM}	30000	W
Peak Forward Surge Current, 8.3ms Sine-Wave Superimposed on Rated Load, (JEDEC Method) (Note 3)	I_{FSM}	400	A
Peak Pulse Current of on 10/1000 μ s Waveform (Note 1)	I_{PPM}	See Next Table	A
Steady State Power Dissipation at T _A =75 °C Lead Lengths.375", (9.5mm) (Note 2)	P_{M(AV)}	8.0	W
Operating junction and storage Temperature range	T_J, T_{STG}	-55 to +175	°C

Notes:

1. Non-repetitive current pulse, per Fig.3 and derated above T_A=25°C per Fig.2.
2. Mounted on Copper Pad area of 0.8x0.8" (20x20mm) per Fig.5.
3. 8.3ms single half sine-wave, or equivalent square wave, Duty cycle=4 pulses per minutes maximum

Electrical Specification ($T_A=25@25^{\circ}\text{C}$ unless otherwise specified)

Part Number		Reverse Stand-Off Voltage	Breakdown Voltage @IT		Test Current	Maximum Clamping Voltage @IPP (V)	Maximum Peak Pulse Current	Maximum Reverse Leakage @VRWM	Package
Uni	Bi	VRWM (V)	VBR MIN(V)	VBR MAX(V)	IT (mA)	VC(V)	IPP (A)	IR(μA)	
30KP28A	30KP28CA	28	31.28	34.41	50	50	606	5000	R6/P600
30KP30A	30KP30CA	30	33.51	36.86	50	55.2	548.9	5000	R6/P600
30KP33A	30KP33CA	33	36.9	40.59	50	58.5	517.9	5000	R6/P600
30KP36A	30KP36CA	36	40.2	44.22	50	61.8	490.3	5000	R6/P600
30KP39A	30KP39CA	39	43.6	47.96	20	67.2	450.9	2000	R6/P600
30KP42A	30KP42CA	42	46.9	51.59	10	72	420.8	1000	R6/P600
30KP43A	30KP43CA	43	48	52.8	10	73	415.1	1000	R6/P600
30KP45A	30KP45CA	45	50.3	55.33	5	77.4	391.5	250	R6/P600
30KP48A	30KP48CA	48	53.6	58.96	5	81.6	371.3	150	R6/P600
30KP51A	30KP51CA	51	57	62.7	5	86.4	350.7	50	R6/P600
30KP54A	30KP54CA	54	60.3	66.33	5	91.4	331.5	20	R6/P600
30KP58A	30KP58CA	58	64.8	71.28	5	92.4	327.9	20	R6/P600
30KP60A	30KP60CA	60	67	73.7	5	102	297.1	15	R6/P600
30KP64A	30KP64CA	64	71.5	78.65	5	104	291.3	10	R6/P600
30KP66A	30KP66CA	66	73.7	81.07	5	107	283.2	5	R6/P600
30KP70A	30KP70CA	70	78.2	86.02	5	109	278	5	R6/P600
30KP71A	30KP71CA	71	79.3	87.23	5	111.5	271.7	5	R6/P600
30KP72A	30KP72CA	72	80.4	88.44	5	114	265.8	5	R6/P600
30KP75A	30KP75CA	75	83.8	92.18	5	119.4	253.8	5	R6/P600
30KP78A	30KP78CA	78	87.1	95.81	5	129	234.9	5	R6/P600
30KP84A	30KP84CA	84	93.8	103.18	5	139.2	217.7	5	R6/P600
30KP90A	30KP90CA	90	100.5	110.55	5	146.4	207	5	R6/P600
30KP96A	30KP96CA	96	107.2	117.92	5	156	194.2	5	R6/P600
30KP102A	30KP102CA	102	113.9	125.29	5	165.6	183	5	R6/P600
30KP108A	30KP108CA	108	120.6	132.66	5	175.2	172.9	5	R6/P600
30KP120A	30KP120CA	120	134	147.4	5	194.4	155.9	5	R6/P600
30KP132A	30KP132CA	132	147.4	162.14	5	213	142.3	5	R6/P600
30KP144A	30KP144CA	144	160.8	176.88	5	223.2	135.8	5	R6/P600
30KP150A	30KP150CA	150	167.6	184.36	5	233.4	129.8	5	R6/P600
30KP156A	30KP156CA	156	174.3	191.73	5	245	123.7	5	R6/P600
30KP160A	30KP160CA	160	178.7	196.57	5	252.6	120	5	R6/P600
30KP168A	30KP168CA	168	187.7	206.47	5	272.4	111.2	5	R6/P600
30KP170A	30KP170CA	170	189.9	208.89	5	275	110.2	5	R6/P600
30KP180A	30KP180CA	180	201.1	221.21	5	290.4	104.3	5	R6/P600
30KP198A	30KP198CA	198	221.2	243.32	5	319.8	94.7	5	R6/P600
30KP216A	30KP216CA	216	241.3	265.43	5	348.6	86.9	5	R6/P600
30KP240A	30KP240CA	240	268.1	294.91	5	387	78.3	5	R6/P600
30KP258A	30KP258CA	258	288.2	317.02	5	416.4	72.8	5	R6/P600
30KP260A	30KP260CA	260	290.4	319.44	5	416	72.8	5	R6/P600
30KP270A	30KP270CA	270	301.6	331.76	5	436.2	69.5	5	R6/P600
30KP280A	30KP280CA	280	312.8	344.08	5	464	65.3	5	R6/P600
30KP288A	30KP288CA	288	321.7	353.87	5	469.9	64.5	5	R6/P600
30KP300A	30KP300CA	300	334	367.4	5	484	62	5	R6/P600
30KP320A	30KP320CA	320	357	391.4	5	530	57.2	5	R6/P600
30KP350A	30KP350CA	350	391	428.1	5	567	53.4	5	R6/P600
30KP360A	30KP360CA	360	402.1	440.3	5	640	47.3	5	R6/P600




FIG. 1 PEAK PULSE POWER RATING

Fig.2 - Pulse Derating Curve





Fig.3 - Pulse Waveform




Ordering information

Package	Packing Description	Packing Quantity
R-6	bulk	100PCS/Inner Box 5000PCS/Carton
	ammo pack	500PCS/Box 5000PCS/Carton

Package Dimensions

R-6

Dim.	Millimeter(mm)		INCHES	
	Min.	Max.	Min.	Max.
A	8.60	9.10	0.340	0.360
B	8.60	9.10	0.340	0.360
C	1.20	1.30	0.048	0.052
D	25.40	-	1.00	-



Disclaimer

The information presented in this document is for reference only. Guangdong Youfeng Microelectronics Co.,Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise. The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), YFW or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale. This publication supersedes & replaces all information previously supplied. For additional information, please visit our website <https://www.yfwdiode.com>, or consult YFW sales office for further assistance.