




Note:
1. Material:
1.1 Housing: thermoplastic high temp.UL94V-0; C
1.2 Latch: thermoplastic high temp.UL94V-0; Col
1.3 Terminal: copper alloy.
1.4 Fitting Nail: copper alloy.
2. Finish:
2.1 Terminal:
Underplating: Au/matt Tin overall.
2.2 Fitting Nail:
Underplating: matt Tin overall.
3. Product must comply HF RoHS specification.

Color: natural.
or: black.

XTS	DIM-A	DIM-B	DIM-C	DIM-D	DIM-E	DIM-F
4P	1.50	2.60	6.50	7.60		
5P	2.00	3.10	7.00	8.10		
6P	2.50	3.60	7.50	8.60		
7P	3.00	4.10	8.00	9.10		
8P	3.50	4.60	8.50	9.60		
9P	4.00	5.10	9.00	10.10		
10P	4.50	5.60	9.50	10.60		
11P	5.00	6.10	10.00	11.10		
12P	5.50	6.60	10.50	11.60		
13P	6.00	7.10	11.00	12.10		
14P	6.50	7.60	11.50	12.60		
15P	7.00	8.10	12.00	13.10		
16P	7.50	8.60	12.50	13.60		
17P	8.00	9.10	13.00	14.10	5.20	6.45
18P	8.50	9.60	13.50	14.60		
19P	9.00	10.10	14.00	15.10		
20P	9.50	10.60	14.50	15.60		
21P	10.00	11.10	15.00	16.10		
22P	10.50	11.60	15.50	16.60		
23P	11.00	12.10	16.00	17.10		
24P	11.50	12.60	16.50	17.60		
25P	12.00	13.10	17.00	18.10		
26P	12.50	13.60	17.50	18.60		
27P	13.00	14.10	18.00	19.10		
28P	13.50	14.60	18.50	19.60		
29P	14.00	15.10	19.00	20.10		
30P	14.50	15.60	19.50	20.60		
31P	15.00	16.10	20.00	21.10		
32P	15.50	16.60	20.50	21.60		
33P	16.00	17.10	21.00	22.10		
34P	16.50	17.60	21.50	22.60		
35P	17.00	18.10	22.00	23.10		
36P	17.50	18.60	22.50	23.60		
37P	18.00	19.10	23.00	24.10		
38P	18.50	19.60	23.50	24.60		
39P	19.00	20.10	24.00	25.10		
40P	19.50	20.60	24.50	25.60		
41P	20.00	21.10	25.00	26.10		
42P	20.50	21.60	25.50	26.60		
43P	21.00	22.10	26.00	27.10		
44P	21.50	22.60	26.50	27.60		
45P	22.00	23.10	27.00	28.10		
46P	22.50	23.60	27.50	28.60		
47P	23.00	24.10	28.00	29.10	5.75	7.00
48P	23.50	24.60	28.50	29.60		
49P	24.00	25.10	29.00	30.10		
50P	24.50	25.60	29.50	30.60		
51P	25.00	26.10	30.00	31.10		
52P	25.50	26.60	30.50	31.60		
53P	26.00	27.10	31.00	32.10		
54P	26.50	27.60	31.50	32.60		
55P	27.00	28.10	32.00	33.10		
56P	27.50	28.60	32.50	33.60		
57P	28.00	29.10	33.00	34.10		
58P	28.50	29.60	33.50	34.60		
59P	29.00	30.10	34.00	35.10		
60P	29.50	30.60	34.50	35.60		

Unit : mm

GENERAL TOLERANCES: (UNLESS SPECIFIED)

0 = ±.20

0.0 = ±.10

0.00 = ±.05

0.000 = ±.03

0' = ± 1'

0.0' = ±.50'

PROJECTION

D.R. 15/04/2022

李小明

CH.K

APV.D

东莞市高钺达电子科技有限公司

惠州市高钺达光电科技有限公司

0.5Pitch H=2.0 FPC 插板下接

CONN.Lower single terminal

SCALE 1:1

SIZE A4

DWG NO. FPCXX-T1T1-2010-A

REV. 01


SH.T NO.1 2

PD./FILE NO. &PRODUCT_NO

C20C0014A

REV. 01


SH.T NO.1 2



- NOTES:
1. 10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE.±0.20mm
 2. CARRIER CAMBER NOT TO EXCEED 1mm IN 250mm.
 3. ALL DIMENSIONS MEET EIA-481-C REQUIREMENTS.
 4. MATERIAL: XXXXX ANTI-STATIC POLYSTYRENE.
 5. THICKNESS: 0.35 ± 0.05 mm.
 6. PACKING LENGTH PER 13" REEL : 24.60METERS.
 7. COMPONENT LOAD PER 13" REEL : 2000PCS.
 8. PEELING OFF FORCE OF TOP TAPE 0.1N~0.7N(10.2gf~71.4gf).

EB-650XXX230-XX

00:黑色
01:白色



CKTS	B0±0.10	W	W1	F	S0±0.10
4	6.70	16±0.3/-0	16.4	7.5±0.10	单边孔
5	7.20				
6	7.70				
7	8.20				
8	8.70				
9	9.20	24±0.3/-0	24.4	11.5±0.10	
10	9.70				
11	10.20				
12	10.70				
13	11.20				
14	11.70	32±0.30	32.4	14.2±0.10	28.4
15	12.20				
16	12.70				
17	13.20				
18	13.70				
19	14.20	44±0.30	44.4	20.2±0.15	40.4
20	14.70				
21	15.20				
22	15.70				
23	16.20				
24	16.70	56±0.30	56.4	26.2±0.15	52.4
25	17.20				
26	17.70				
27	18.20				
28	18.70				
29	19.20	68±0.30	68.4	32.2±0.15	68.4
30	19.70				
31	20.20				
32	20.70				
33	21.20				
34	21.70	80±0.30	80.4	38.2±0.15	84.4
35	22.20				
36	22.70				
37	23.20				
38	23.70				
39	24.20	92±0.30	92.4	44.2±0.15	96.4
40	24.70				
41	25.20				
42	25.70				
43	26.20				
44	26.70	104±0.30	104.4	50.2±0.15	104.4
45	27.20				
46	27.70				
47	28.20				
48	28.70				
49	29.20	116±0.30	116.4	56.2±0.15	112.4
50	29.70				
51	30.20				
52	30.70				
53	31.20				
54	31.70	128±0.30	128.4	62.2±0.15	124.4
55	32.20				
56	32.70				
57	33.20				
58	33.70				
59	34.20	140±0.30	140.4	68.2±0.15	136.4
60	34.70				

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参考表		东莞市高钱达电子科技有限公司 惠州市高钱达光电科技有限公司			
X.X : ±0.15	X.X° : ±5°	APPD: 核准: ZHANGHAO	PART NO.		
X.XX : ±0.10	X.XX° : ±3°	CHECK: JOHNSON	TITLE: 产品名称: FPC 0.5mm 2.0H载带图		
X.XXX : ±0.05	X.XXX° : ±1°	DRAW: HOHNSON	DATE	SCALE	UNIT
		繪圖:	20110907	1:1	mm
					1/1

		文件編號：	
		修訂日期：	2021-09-26
0.5mm 2.0H FPC/FFC	Product Specification	版 次：	Rev A
		頁 次：	1 of 7

【1】 适用范围 SCOPE

本规格书适用于 0.5mmPitch FPC 拉拔卧式 SMT 型连接器系列.
This specification covers the 0.5mmPitch FPC ZIF R/A SMT Type Connectors series.

【2】 外观尺寸 CONNECTOR DIMENSIONS

请参照图面
See attached drawings.

【3】 材质 MATERIAL

绝缘胶体 Housing: LCP
颜色 Color:白色 White
耐燃等级 (UL94V-0)Flammability Rating (UL94V-0).
后盖 Actuator: LCP
颜色 Color:黑色 Black
耐燃等级 (UL94V-0)Flammability Rating (UL94V-0).
端子 Terminal: 磷青铜 Phosphor Bronze.
焊片 Fitting Nail:黄铜 Brass.

【4】 建议 P. C. B LAYOUT 图 ACCOMMODATED P. C. B LAYOUT

请参照图面
See attached drawings.

【5】 等级 RATING

项 目 ITEM	规 格 SPECIFICATIONS
最大容许电压 Operating Voltage(Max.)	50V AC
最大容许电流 Current Rating(Max.)	0.4A DC
使用温度范围 Operating Temperature range	-25℃～+85℃
使用湿度范围 Operating humidity range	相对湿度90%以下 Relative humidity 90% max.
保存温度范围 Storage temperature range	-10℃ ～ +50℃
保存湿度范围 Storage humidity range	相对湿度90%以下 Relative humidity 90% max.

*: 包含电流通过所产生的上升温度 Including terminal temperature rise.

		文件編號：	
		修訂日期：	2021-09-26
0.5mm 2.0H FPC/FFC	Product Specification	版 次：	Rev A
		頁 次：	2 of 7

【6】 性能 PERFORMANCE

6.1 电气特性 ELECTRICAL PERFORMANCE

项目 ITEM	测试条件 TEST CONDITION	规格 REQUIRMENT
接触阻抗 Contact Resistance	将样品与适合之FPC连接，测试电压20mV，限电流10mA下进行阻抗测试。(EIA-364-23) Mate applicable FPC and measure by dry circuit, 20mV Max, 10mA. (EIA-364-23)	40 mΩ最大. 40 mΩ Max.
绝缘阻抗 Insulation Resistance	将样品与适合之FPC连接，提供相邻端子间测试电压500V DC进行绝缘阻抗测试(EIA-364-21) Mate applicable FPC and apply 500V DC between adjacent terminal or ground. (EIA-364-21)	500MΩ最小. 500 MΩ Min.
耐电压 Dielectric Strength	将样品与适合之FPC连接，相邻端子间需可承受250V AC(rms) 1分钟。(EIA-364-20) Mate applicable FPC, apply 250V AC(rms) for1 minute between adjacent terminal or ground.(EIA-364-20)	目视外观无任何损坏异状 No Breakdown

6.2 机械特性 MECHANICAL PERFORMANCE

项目 ITEM	测试条件 TEST CONDITION	规格 REQUIRMENT
FPC保持力 FPC Retention Force	将盖子盖上，与FPC连接，以操作速度每分钟位移25±3mm进行FPC保持力测试。 Insert the actuator, pull the FPC at a rate of 25±3mm per minute.	Pos.x 0.3N最小 Pos.x 0.3N Min.
端子保持力 Terminal Retention Force	端子与Housing组装后，以操作速度每分钟位移25±3mm将端子拔出Housing，进行端子保持力测试。 Apply axial pull out force at the rate of 25±3 mm/minute on the terminal assembled in the housing.	3N最小. 3N Min.

0.5mm 2.0H FPC/FFC		Product Specification		文件編號：	
				修訂日期：	
				版 次：	
				頁 次：	
				2021-09-26	
				Rev A	
				3 of 7	
项目 ITEM		测试条件 TEST CONDITION		规格 REQUIRMENT	
焊片保持力 Fitting Nail Retention Force		焊片与Housing组装后，以操作速度每分钟位移25±3mm将焊片拔出Housing，进行焊片保持力测试。 Apply axial pull out force at the rate of 25±3 mm/minute on the Fitting Nail assembled in the housing.		1N最小. 1N Min	
6. 3 环境特性及其它性能 ENVIRONMENTAL PERFORMANCE AND OTHERS					
项目 ITEM		测试条件 TEST CONDITION		规格 REQUIRMENT	
耐久性 Durability		将盖子与FPC反复连接，以每分钟小于10 cycles连续操作20次。 Insert and withdraw actuator up to 20 cycles at the speed rate of less than 10 cycles/minute.		接触阻抗 Contact Resistance	60mΩ最大. 60mΩ Max.
温度上升 Temperature Rise		量测通过FPC最大容许电流时，样品接 触 点 之 温 升 (EIA-364-70 METHOD 2) Mate applicable FPC and measure the temperature rise of contact when the maximum AC rated current is passed. (EIA-364-70 METHOD 2)		温升 Temperature rise	30℃最大. 30℃ Max.
耐振性 Vibration		通过DC电流1mA，位移相对距离1.5mm，振动周期10～55～10 Hz在1分钟内，持续2小时，方向在X,Y,Z轴做测试。(EIA-364-28 Condition I) Mate connectors and subject to the following vibration conditions, for period of 2 hours in each of 3 mutually perpendicular axes, passing DC 1mA during the test. Amplitude：1.5mm P-P Frequency：10～55～10 Hz in 1 minute. Duration：2 hours in each of X,Y,Z axes. (EIA-364-28 Condition I)		外观 Appearance	目视外观无任何损坏异状 NoDamage
				接触阻抗 Contact Resistance	60mΩ最大. 60mΩ Max.
				瞬间断电 Discontinuity	1 μ sec最大 1 μ sec Max.


0.5mm 2.0H FPC/FFC		Product Specification		文件編號：	
				修訂日期：	
				版 次：	
				頁 次：	
				2021-09-26	
				Rev A	
				4 of 7	
項目 ITEM		測試條件 TEST CONDITION		規格 REQUIRMENT	
耐衝擊性 Shock		將樣品與適合之FPC連接，通過DC 1 mA測試條件，連續測試3次。在X、Y、Z 3軸6個垂直方向施予重力加速度490m/s2 {50G} 衝擊。 (EIA-364-27, test condition A) Mate applicable FPC and subject to the following shock conditions. 3 times of shocks shall be applied for each 6 directions along 3 mutually perpendicular axes, passing DC 1 mA current during the test. (Total of 18 shocks) Peak value : 490m/s2 {50G}(EIA-364-27, test condition A)		外觀 Appearance	目視外觀無任何損壞異狀 NoDamage
				接觸阻抗 Contact Resistance	60mΩ 最大. 60mΩ Max.
				瞬間斷電 Discontinuity	1 μ sec 最大 1 μ sec Max.
耐熱性 Heat Resistance		將樣品與適合之FPC連接，置於環境溫度85±2℃測試時間96小時，再置放於室溫下1～2小時。 Mate applicable FPC and expose to 85±2℃ for 96 hours. Upon completion of the exposure period, the test specimens shall be conditioned at ambient room conditions for 1 to 2 hours, after which the specified measurements shall be performed.		外觀 Appearance	目視外觀無任何損壞異狀 NoDamage
				接觸阻抗 Contact Resistance	60mΩ 最大. 60mΩ Max.
耐寒性 Cold Resistance		將樣品與適合之FPC連接，置於環境溫度-40±2℃，測試時間96小時，再置放於室溫下1～2小時。 Mate applicable FPC and expose to -40±2℃ for 96 hours. Upon completion of the exposure period, the test specimens shall be conditioned at ambient room conditions for 1 to 2 hours, after which the specified measurements shall be performed.		外觀 Appearance	目視外觀無任何損壞異狀 NoDamage
				接觸阻抗 Contact Resistance	60mΩ 最大. 60mΩ Max.

0.5mm 2.0H FPC/FFC		Product Specification		文件編號：	
				修訂日期：	
				版 次：	
				頁 次：	
				2021-09-26	
				Rev A	
				5 of 7	
項目 ITEM		測試條件 TEST CONDITION		規格 REQUIRMENT	
耐濕性 Humidity		將樣品與適合之FPC連接，置於環境溫度60±2°C，相對濕度90～95%，測試時間96小時，再置放於室溫下1～2小時。 Mate applicable FPC and expose to 60 ± 2°C, relative humidity 90 to 95% for 96 hours. Upon completion of the exposure period, the test specimens shall be conditioned at ambient room conditions for 1 to 2 hours, after which the specified measurements shall be performed.		外觀 Appearance	目視外觀無任何損壞異狀 NoDamage
				接觸阻抗 Contact Resistance	60mΩ最大. 60mΩMax.
				耐電壓 Dielectric Strength	需能符合耐電壓測試 No Breakdown
				絕緣阻抗 Insulation t Resistance	40 MΩ 最小. 40 MΩ Min
冷熱沖擊 Temperature Cycling		將樣品與適合之FPC連接，承受5 cycles冷熱沖擊後置放於室溫下1～2小時。1 cycle time如下 a) -55±3°C 30分鐘 b) +85±3°C 30分鐘 Mate applicable FPC and subject to the following conditions for 5 cycles. Upon completion of the exposure period, the test specimens shall be conditioned at ambient room conditions for 1 to 2 hours, after which the specified measurements shall be performed. 1 cycle a) -55±3°C 30minutes b) +85±3°C 30minutes		外觀 Appearance	目視外觀無任何損壞異狀 NoDamage
				接觸阻抗 Contact Resistance	60mΩ 最大. 60mΩ Max.
鹽水噴霧 Salt Spray		將樣品與適合之FPC連接，使用5±1%濃度鹽水，測試溫度35±2°C，測試時間 8±4小時,後於室溫下使用清水沖洗後再乾燥。 Mate applicable FPC and expose to the following salt mist conditions. Upon completion of the exposure period, salt deposits shall be removed by a gentle wash or dip in running water, after which the specified measurements shall be performed. NaCl solution Concentration : 5 ± 1% Spray time : 8 ± 4 hours Ambient temperature : 35 ± 2°C		外觀 Appearance	目視外觀無任何損壞異狀 NoDamage
				接觸阻抗 Contact Resistance	60mΩ 最大. 60mΩ Max.

0.5mm 2.0H FPC/FFC		Product Specification		文件編號：	
				修訂日期：	
				版 次：	
				頁 次：	
				2021-09-26	
				Rev A	
				6 of 7	
项目 ITEM		测试条件 TEST CONDITION		规格 REQUIRMENT	
二氧化硫(气体) SO2 Gas		将样品与适合之FPC连接，将其置放于50±5 ppm浓度二氧化硫气体中，测试温度40±2℃，测试时间24小时。 Mate applicable FPC and expose them to the following SO2 gas atmosphere. Temperature 40 ± 2℃ Gas Density 50 ± 5 ppm Duration 24 hours		外观 Appearance	目视外观无任何损坏异状 NoDamage
				接触阻抗 Contact Resistance	60mΩ 最大. 60mΩ Max.
氨(气体) NH3 Gas		暴露来自浓度28%阿摩尼亚之蒸发气体NH3中，测试时间40分钟。 40 minutes exposure to NH3 gas evaporating from28% Ammonia solution.		外观 Appearance	目视外观无任何损坏异状 NoDamage
				接触阻抗 Contact Resistance	60mΩ 最大. 60mΩ Max.
焊锡性 Solderability		锡温245±5℃，将导电端子浸入锡炉液面至Housing距离锡面0.1mm位置，焊锡时间3±0.5秒。 Tip of solder tails and fitting nails into the molten solder (held at 245±5℃) up to 0.1mm from the bottom of the housing for 3±0.5 seconds.		润湿性 Solder Wetting	润湿面积75%以上，并不得有漏焊针孔现象 75% of immersed area must show no voids, pin holes.
焊锡耐热性 Resistance to Soldering Heat		使用红外线回焊时请参考第7 When reflowing Refer to paragraph 7. 使用烙铁手焊时须可符合下述焊锡条件 Soldering iron method 0.3mm from terminal tip and fitting nail tip. Soldering time : 3 seconds Max. Solder temperature : 370～400℃		外观 Appearance	目视外观无任何损坏异状 NoDamage

		文件編號：	
		修訂日期：	2021-09-26
0.5mm 2.0H FPC/FFC	Product Specification	版 次：	Rev A
		頁 次：	7 of 7

【7】 红外线回焊温度曲线 INFRARED REFLOW CONDITION



温度条件TEMPERATURE CONDITION GRAPH
(基板表面温度) (TEMPERATURE ON BOARD PATTERN SIDE)