

FEATURES

- * Ideal for surface mount applications
- * Easy pick and place
- * Built-in strain relief
- * Low forward voltage drop

MECHANICAL DATA

- * Case: Molded plastic
- * Epoxy: UL 94V-0 rate flame retardant
- * Metallurgically bonded construction
- * Polarity: Color band denotes cathode end
- * Mounting position: Any
- * Weight: 0.063 grams





VOLTAGE RANGE

40 Volts

CURRENT

2.0 Ampere



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating 25°C ambient temperature unless otherwise specified.
Single phase half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

TYPE NUMBER	SL24B	UNITS
Maximum Recurrent Peak Reverse Voltage	40	V
Maximum RMS Voltage	28	V
Maximum DC Blocking Voltage	40	V
Maximum Average Forward Rectified Current See Fig. 1	2.0	A
Peak Forward Surge Current, 8.3 ms single half sine-wave superimposed on rated load (JEDEC method)	50	A
Maximum Instantaneous Forward Voltage at 2.0A	0.46	V
Maximum DC Reverse Current Ta=25°C	0.2	mA
at Rated DC Blocking Voltage Ta=125°C	50	mA
Typical Junction Capacitance (Note1)	170	pF
Typical Thermal Resistance R JA (Note 2)	88	°C/W
Operating Temperature Range Tj	-55 to +125	°C
Storage Temperature Range Tstg	-55 to +150	°C

NOTES:

1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.
2. P.C.B. mounted with 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pad areas

RATING AND CHARACTERISTIC CURVES

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2-TYPICAL FORWARD CHARACTERISTICS




FIG.3 - TYPICAL REVERSE CHARACTERISTICS




FIG.4-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT






FIG.5-TYPICAL JUNCTION CAPACITANCE




Soldering parameters

Reflow Condition		Pb-Free assembly (see as below)
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150°C
	-Temperature Max($T_{s(max)}$)	+200°C
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3°C/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/sec. Max
Reflow	-Temperature(T_L)(Liquid us)	+217°C
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_P)		+260(+0/-5)°C
Time within 5°C of actual Peak Temp (t_P)		30 secs. Max
Ramp-down Rate		6°C/sec. Max
Time 25°C to Peak Temp (T_P)		8 min. Max
Do not exceed		+260°C




Package Dimensions & Suggested Pad Layout

SMB






SMB		
Dim	Min	Max
A	3.30	3.94
B	4.06	4.70
C	1.91	2.11
D	0.15	0.31
E	5.08	5.59
G		0.20
H	0.76	1.50
J	2.13	2.44
All Dimensions in mm		



Dimensions	Value (in mm)
C	4.70
G	2.20
X	2.50
X1	7.20
Y	2.80

Tape & reel specification

Tape  SECTION : A-A SECTION : B-B	<table> <tr> <th>Symbol</th><th>Dimension (mm)</th></tr> <tr><td>P0</td><td>4.00±0.20</td></tr> <tr><td>P1</td><td>8.00±0.20</td></tr> <tr><td>P2</td><td>2.00±0.20</td></tr> <tr><td>D0</td><td>1.60±0.20</td></tr> <tr><td>D1</td><td>1.60±0.20</td></tr> <tr><td>E</td><td>1.75±0.20</td></tr> <tr><td>F</td><td>5.50±0.15</td></tr> <tr><td>W</td><td>12.00±0.20</td></tr> <tr><td>A0</td><td>4.00±0.20</td></tr> <tr><td>B0</td><td>5.45±0.20</td></tr> <tr><td>K0</td><td>2.50±0.25</td></tr> <tr><td>T</td><td>0.20±0.10</td></tr> </table>	Symbol	Dimension (mm)	P0	4.00±0.20	P1	8.00±0.20	P2	2.00±0.20	D0	1.60±0.20	D1	1.60±0.20	E	1.75±0.20	F	5.50±0.15	W	12.00±0.20	A0	4.00±0.20	B0	5.45±0.20	K0	2.50±0.25	T	0.20±0.10
Symbol	Dimension (mm)																										
P0	4.00±0.20																										
P1	8.00±0.20																										
P2	2.00±0.20																										
D0	1.60±0.20																										
D1	1.60±0.20																										
E	1.75±0.20																										
F	5.50±0.15																										
W	12.00±0.20																										
A0	4.00±0.20																										
B0	5.45±0.20																										
K0	2.50±0.25																										
T	0.20±0.10																										
7" Reel 	<table> <tr><td>D2</td><td>176.0±5.0</td></tr> <tr><td>D3</td><td>55.0Min.</td></tr> <tr><td>D4</td><td>14.0±2.5</td></tr> <tr><td>W1</td><td>14.0±2.5</td></tr> <tr><td colspan="2">Quantity: 3000PCS</td></tr> </table>	D2	176.0±5.0	D3	55.0Min.	D4	14.0±2.5	W1	14.0±2.5	Quantity: 3000PCS																	
D2	176.0±5.0																										
D3	55.0Min.																										
D4	14.0±2.5																										
W1	14.0±2.5																										
Quantity: 3000PCS																											
13" Reel 	<table> <tr><td>D5</td><td>330.0±5.0</td></tr> <tr><td>D6</td><td>73.0Min.</td></tr> <tr><td>D7</td><td>14.0±2.5</td></tr> <tr><td>W2</td><td>16.0±2.5</td></tr> <tr><td colspan="2">Quantity: 5000PCS</td></tr> </table>	D5	330.0±5.0	D6	73.0Min.	D7	14.0±2.5	W2	16.0±2.5	Quantity: 5000PCS																	
D5	330.0±5.0																										
D6	73.0Min.																										
D7	14.0±2.5																										
W2	16.0±2.5																										
Quantity: 5000PCS																											