


客户图



Note:

- Material(材料):
 - Barrel: Brass C3604 (针管: 黄铜 C3604)
 - Plunger: Brass C3604 (针头: 黄铜 C3604)
 - Spring: SUS304 (弹簧: SUS304)
- Plating(电镀):
 - Barrel: 3u' Au over 80~120u' Ni over 80~120u' Cu(针管: 镀金3u', 镍底80~120u', 铜底80~120u'.)
 - Plunger: 3u' Au over 80~120u' Ni over 80~120u' Cu(针头: 镀金3u', 镍底80~120u', 铜底80~120u'.)
 - Spring: Gold flash (弹簧: 镀金)
- Electrical(电气特性):
 - Rated Current & Voltage: DC 12V;3A (额定电压&电流: 直流12V,3A)
 - Contact Resistance: 50 mohm Max. at working height.
 - 接触电阻: 最大50毫欧 (在工作高度状态下)
- Mechanical(机械性能):
 - Force: $50g \pm 20\%$ at working height. ($50g \pm 20\%$ 在工作高度)。
 - Durability: 10.000 cycles(min) (寿命: 10000次)
- WorkTemperture(工作环境):
 - Withstanding Higt Temperature: 280℃
 - Operational Temperature: $-20^{\circ}\text{C} \sim +70^{\circ}\text{C}$

深圳市鑫扬泽电子有限公司



TEL:0755-28773277 FAX:0755-28891353

SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2022.12.05	VER.	A.0

THE UNMARKED TOLERANCE ARE AS BELOW :

LENGTH		ANGLE	
X.XX	$\pm 0.05\text{mm}$	X.XX	$\pm 0.50^{\circ}$
X.X	$\pm 0.10\text{mm}$	X.X	$\pm 1.00^{\circ}$
X.	$\pm 0.20\text{mm}$	X.	$\pm 2.00^{\circ}$

DESIGNED BY:		DWG. NO.	YZP0733-28095-01
CHECKED BY:		TITLE:	POGO PIN
APPROVED BY:			