





NOTE:

- MATERIAL SPECIFICATION:
 - HOUSING: HIGH TEMPERATURE RESISTANT PLASTIC UL 94 V-0
 - CONTACTS: COPPER ALLOY
 - MID PLATE: STAINLESS STEEL
 - SHELL: STAINLESS STEEL
- PLATING SPECIFICATION:
 - CONTACTS:
 - Ni 50u"MIN UNDER PLATED OVER ALL
 - Au PLATED ON THE FUNCTIONAL AREA OF CONTACT
 - TIN 100u"MIN ON THE SOLDER AREA OF CONTACT
 - SHELL:
 - Ni 30u"MIN UNDER PLATED OVER ALL
- MECHANICAL PERFORMANCE:
 - INSERTION FORCE: 5-20N
 - REMOVAL FORCE: 8-20N
 - DURABILITY: 10000 CYCLES
- ELECTRICAL PERFORMANCE:
 - CURRENT RATING: 5.0 A
 - LLCR:
 - VBUS&GND PINS AND OTHER PINS: 40mΩ /PIN MAX
 - SHIELD: 50mΩ MAX
 - LLCR MAX CHANGE OF ALL PINS 10mΩ
 - INSULATION RESISTANCE: 100MΩ MIN
 - DIELECTRIC WITHSTAND VOLTAGE: AC 100V FOR 1 MINUTE
- ENVIRONMENTAL PERFORMANCE: -25° C ~ +85° C
- IR REFLOW PERFORMANCE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260° C



07	外壳	不锈钢	1	SUS 304 1/2H,T0.30
06	二次Molding件	LCP	1	黑色 UL94 V-0
05	Molding件2	LCP	1	黑色 UL94 V-0
04	Molding件1	LCP	1	黑色 UL94 V-0
03	中夹片	SUS301-H T=0.15	1	不电镀
01	端子	C2680-H T=0.15	1set	功能接触区镀金, 焊脚镀金
序号	品名	材质	用量	备注

UNLESS OTHERWISE
SPECIFIED TOLERANCES



DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.15



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD



TITLE	TYPE C 16P 立式贴片5.0带两个固定脚黄铜			
DWN	xiong	PART NO. MC-140LS-H50		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY










NOTE:

- MATERIAL SPECIFICATION:
 - HOUSING: HIGH TEMPERATURE RESISTANT PLASTIC UL 94 V-0
 - CONTACTS: COPPER ALLOY
 - MID PLATE: STAINLESS STEEL
 - SHELL: STAINLESS STEEL
- PLATING SPECIFICATION:
 - CONTACTS:
 - Ni 50u"MIN UNDER PLATED OVER ALL
 - Au PLATED ON THE FUNCTIONAL AREA OF CONTACT
 - TIN 100u"MIN ON THE SOLDER AREA OF CONTACT
 - SHELL:
 - Ni 30u"MIN UNDER PLATED OVER ALL
- MECHANICAL PERFORMANCE:
 - INSERTION FORCE: 5-20N
 - REMOVAL FORCE: 8-20N
 - DURABILITY: 10000 CYCLES
- ELECTRICAL PERFORMANCE:
 - CURRENT RATING: 5.0 A
 - LLCR:
 - VBUS&GND PINS AND OTHER PINS: 40mΩ/PIN MAX
 - SHIELD: 50mΩ MAX
 - LLCR MAX CHANGE OF ALL PINS 10mΩ
 - INSULATION RESISTANCE: 100MΩ MIN
 - DIELECTRIC WITHSTAND VOLTAGE: AC 100V FOR 1 MINUTE
- ENVIRONMENTAL PERFORMANCE: -25° C ~ +85° C
- IR REFLOW PERFORMANCE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260° C






07 外壳	不锈钢	1	SUS 304 1/2H,T0.30	
06 二次Molding件	LCP	1	黑色 UL94 V-0	
05 Molding件2	LCP	1	黑色 UL94 V-0	
04 Molding件1	LCP	1	黑色 UL94 V-0	
03 中夹片	SUS301-H T=0.15	1	不电镀	
01 端子	C2680-H T=0.15	1set	功能接触区镀金, 焊脚镀金	
序号	品名	材质	用量	备注
UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD		
DECIMALS:		ANGLES:	TITLE	
X :±0.30		X :±2°	DWN	xiong
X.X :±0.20		X.X :±1°	CHKD	lee
X.XX :±0.15			APVD	wang
			TYPE C 16P 立式贴片5.5带两个固定脚黄铜	
			PART NO. MC-140LS-H55	
			SCALE:1:1 UNIT: mm	
			SIZE: A4 SHEET:10F 1	
			REV: A4	
			CUSTOMER COPY	



NOTE:





- MATERIAL SPECIFICATION:
 - HOUSING:HIGH TEMPERATURE RESISTANT PLASTIC UL 94 V-0
 - CONTACTS: COPPER ALLOY
 - MID PLATE: STAINLESS STEEL
 - SHELL: STAINLESS STEEL
- PLATING SPECIFICATION:
 - CONTACTS:
 - Ni 50u"MIN UNDER PLATED OVER ALL
 - Au PLATED ON THE FUNCTIONAL AREA OF CONTACT
 - TIN 100u"MIN ON THE SOLDER AREA OF CONTACT
 - SHELL:
 - Ni 30u"MIN UNDER PLATED OVER ALL
- MECHANICAL PERFORMANCE:
 - INSERTION FORCE: 5-20N
 - REMOVAL FORCE: 8-20N
 - DURABILITY: 10000 CYCLES
- ELECTRICAL PERFORMANCE:
 - CURRENT RATING: 5.0 A
 - LLCR:
 - VBUS&GND PINS AND OTHER PINS: 40mΩ/PIN MAX
 - SHIELD: 50mΩ MAX
 - LLCR MAX CHANGE OF ALL PINS 10mΩ
 - INSULATION RESISTANCE: 100MΩ MIN
 - DIELECTRIC WITHSTAND VOLTAGE: AC 100V FOR 1 MINUTE
- ENVIRONMENTAL PERFORMANCE: -25° C ~ +85° C
- IR REFLOW PERFORMANCE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260° C

07 外壳	不锈钢	1	SUS 304 1/2H,T0.30	
06 二次Molding件	LCP	1	黑色 UL94 V-0	
05 Molding件2	LCP	1	黑色 UL94 V-0	
04 Molding件1	LCP	1	黑色 UL94 V-0	
03 中夹片	SUS301-H T=0.15	1	不电镀	
01 端子	C2680-H T=0.15	1set	功能接触区镀金, 焊脚镀金	
序号	品名	材质	用量	备注
UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD		
DECIMALS:		TITLE	TYPE C 16P立式贴片5.8带两个固定脚黄铜	
X	±0.30	DWN	xiong	PART NO. MC-140LS-H58
X.X	±0.20	CHKD	lee	SCALE:1:1 UNIT: mm
X.XX	±0.15	APVD	wang	SIZE: A4 SHEET:10F 1 REV: A4
CUSTOMER COPY				



NOTE:

- MATERIAL SPECIFICATION:
 - HOUSING: HIGH TEMPERATURE RESISTANT PLASTIC UL 94 V-0
 - CONTACTS: COPPER ALLOY
 - MID PLATE: STAINLESS STEEL
 - SHELL: STAINLESS STEEL
- PLATING SPECIFICATION:
 - CONTACTS:
 - Ni 50u"MIN UNDER PLATED OVER ALL
 - Au PLATED ON THE FUNCTIONAL AREA OF CONTACT
 - TIN 100u"MIN ON THE SOLDER AREA OF CONTACT
 - SHELL:
 - Ni 30u"MIN UNDER PLATED OVER ALL
- MECHANICAL PERFORMANCE:
 - INSERTION FORCE: 5-20N
 - REMOVAL FORCE: 8-20N
 - DURABILITY: 10000 CYCLES
- ELECTRICAL PERFORMANCE:
 - CURRENT RATING: 5.0 A
 - LLCR:
 - VBUS&GND PINS AND OTHER PINS: 40mΩ/PIN MAX
 - SHIELD: 50mΩ MAX
 - LLCR MAX CHANGE OF ALL PINS 10mΩ
 - INSULATION RESISTANCE: 100MΩ MIN
 - DIELECTRIC WITHSTAND VOLTAGE: AC 100V FOR 1 MINUTE
- ENVIRONMENTAL PERFORMANCE: -25° C ~ +85° C
- IR REFLOW PERFORMANCE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260° C



07	外壳	不锈钢	1	SUS 304 1/2H,T0.30
06	二次Molding件	LCP	1	黑色 UL94 V-0
05	Molding件2	LCP	1	黑色 UL94 V-0
04	Molding件1	LCP	1	黑色 UL94 V-0
03	中夹片	SUS301-H T=0.15	1	不电镀
01	端子	C2680-H T=0.15	1set	功能接触区镀金, 焊脚镀金
序号	品名	材质	用量	备注

UNLESS OTHERWISE
SPECIFIED TOLERANCES





DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.15




东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	TYPE C 16P 立式贴片6.0带两个固定脚黄铜			
DWN	xiong	PART NO. MC-140LS-H60		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:1OF 1	REV: A4

CUSTOMER COPY





CONTACT DEFINITION (16P)



NOTE:

- MATERIAL SPECIFICATION:
 - HOUSING: HIGH TEMPERATURE RESISTANT PLASTIC UL 94 V-0
 - CONTACTS: COPPER ALLOY
 - MID PLATE: STAINLESS STEEL
 - SHELL: STAINLESS STEEL
- PLATING SPECIFICATION:
 - CONTACTS:
 - Ni 50u"MIN UNDER PLATED OVER ALL
 - Au PLATED ON THE FUNCTIONAL AREA OF CONTACT
 - TIN 100u"MIN ON THE SOLDER AREA OF CONTACT
 - SHELL:
 - Ni 30u"MIN UNDER PLATED OVER ALL
- MECHANICAL PERFORMANCE:
 - INSERTION FORCE: 5-20N
 - REMOVAL FORCE: 8-20N
 - DURABILITY: 10000 CYCLES
- ELECTRICAL PERFORMANCE:
 - CURRENT RATING: 5.0 A
 - LLCR:
 - VBUS&GND PINS AND OTHER PINS: 40mΩ/PIN MAX
 - SHIELD: 50mΩ MAX
 - LLCR MAX CHANGE OF ALL PINS 10mΩ
 - INSULATION RESISTANCE: 100MΩ MIN
 - DIELECTRIC WITHSTAND VOLTAGE: AC 100V FOR 1 MINUTE
- ENVIRONMENTAL PERFORMANCE: -25° C ~ +85° C
- IR REFLLOW PERFORMANCE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260° C



07	外壳	不锈钢	1	SUS 304 1/2H.T0.30
06	二次Molding件	LCP	1	黑色 UL94 V-0
05	Molding件2	LCP	1	黑色 UL94 V-0
04	Molding件1	LCP	1	黑色 UL94 V-0
03	中夹片	SUS301-H T=0.15	1	不电镀
01	端子	C2680-H T=0.15	1set	功能接触区镀金, 焊脚镀金
序号	品名	材质	用量	备注

UNLESS OTHERWISE
SPECIFIED TOLERANCES




DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.15



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD






TITLE	TYPE C 16P 立式贴片6.5带两个固定脚黄铜			
DWN	xiong	PART NO. MC-140LS-H65		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:1OF 1	REV: A4

CUSTOMER COPY



NOTE:

- MATERIAL SPECIFICATION:
 - HOUSING: HIGH TEMPERATURE RESISTANT PLASTIC UL 94 V-0
 - CONTACTS: COPPER ALLOY
 - MID PLATE: STAINLESS STEEL
 - SHELL: STAINLESS STEEL
- PLATING SPECIFICATION:
 - CONTACTS:
 - Ni 50u"MIN UNDER PLATED OVER ALL
 - Au PLATED ON THE FUNCTIONAL AREA OF CONTACT
 - TIN 100u"MIN ON THE SOLDER AREA OF CONTACT
 - SHELL:
 - Ni 30u"MIN UNDER PLATED OVER ALL
- MECHANICAL PERFORMANCE:
 - INSERTION FORCE: 5-20N
 - REMOVAL FORCE: 8-20N
 - DURABILITY: 10000 CYCLES
- ELECTRICAL PERFORMANCE:
 - CURRENT RATING: 5.0 A
 - LLCR:
 - VBUS&GND PINS AND OTHER PINS: 40mΩ/PIN MAX
 - SHIELD: 50mΩ MAX
 - LLCR MAX CHANGE OF ALL PINS 10mΩ
 - INSULATION RESISTANCE: 100MΩ MIN
 - DIELECTRIC WITHSTAND VOLTAGE: AC 100V FOR 1 MINUTE
- ENVIRONMENTAL PERFORMANCE: -25° C ~ +85° C
- IR REFLOW PERFORMANCE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260° C



07	外壳	不锈钢	1	SUS 304 1/2H,T0.30
06	二次Molding件	LCP	1	黑色 UL94 V-0
05	Molding件2	LCP	1	黑色 UL94 V-0
04	Molding件1	LCP	1	黑色 UL94 V-0
03	中夹片	SUS301-H T=0.15	1	不电镀
01	端子	C2680-H T=0.15	1set	功能接触区镀金, 焊脚镀金
序号	品名	材质	用量	备注
UNLESS OTHERWISE SPECIFIED TOLERANCES		 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD		
DECIMALS: ANGLES:		TITLE TYPE C 16P立式贴片6.8带两个固定脚黄铜		
X :±0.30	X :±2°	DWN	xiong	PART NO. MC-140LS-H68
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1 UNIT: mm 
X.XX :±0.15		APVD	wang	SIZE: A4 SHEET:1OF 1 REV: A4
CUSTOMER COPY				



A

A

B

B

C


C

D

D


E

E




客户拉出方向


自粘上带(上带剥离力0.2-1.2N)
前端



产品内标签
产品标签格式(所有包装格式一致,只需更改数量即可)




卷带盘10盘




10盘


将10盘产品放入纸箱内




空120mm(10PCS)



6.0M(500PCS)



空120mm(10PCS)



产品外标签

备注:

1. 把上下载带送入载带机进行调整,然后将产品按照指定的方式摆入下载带中,开动卷带机进行卷装(每卷包600PCS),卷装完成后需用美纹胶缠绕最少15CM;
2. 在卷装OK的每卷盘面的指定位置上贴上物料和RoHS标签装入纸箱内;每箱装10盘
3. 纸箱用封箱带将其封好,胶带要求工字型,不可遮住标签;
4. 如果客户对包装标签另有要求,请按客户要求作业;有未满之零数箱需用缓冲材料填充;
5. 上载带剥离力:0.2-1.2N

包装明细表 (The detail of the packing) Carton			
产品料号 (Product No.)	包装容量 (Packing Capacity)		
	pcs/box	boxs/Carton	Pcs/Box
MC-140LS	600	10	6000

纸箱规格:
35.0X35.0X33.0CM

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS:	ANGLES:	TITLE	TYPE C 16P 立式贴片6.8带两个固定脚黄铜		
X :±0.30	X :±2°	DWN	xiong	PART NO. MC-140LS-HXXX	
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm
X.XX :±0.15		APVD	wang	SIZE: A4	SHEET:10F 1
CUSTOMER COPY					