








1.88
(Min.compression)
1.78
(Working height)
1.68
(Max.compression)



STATED AT COMPRESSION
(FOR REFERENCE ONLY)



RECOMMENDED PCB LAYOUT
TOLERANCE±0.05(焊盘推荐图)
(FOR REFERENCE ONLY)



3D VIEW

NOTES:

1:MATERIAL:

1-1:COPPER ALLOY THICKNE=0.08mm

2:FINISH:

2-1:SEE DETAILED LIST.

3:PRODUCT SPECIFICATIONS:

3-1:RATED CURRENT:1.0A/MAX

3-2:VOLTAGE RATING:1.50V/AC/DC/MAX

3-3:CONTACT RESISTANCE:80mΩ/MAX

3-4:OPERATING TEMPERATURE:-40°C~85°C

3-5:NORMAL FORCE OF PRESS@1.78MM:0.50N MIN ON CONTACT POINT.

3-6:DURABILITY:1,500 CYCLES.

4:SALT SPRAY:SEE DETAILED LIST.

5:PACKING SPECIFICATION:REEL&TARE

6:DIMENSIONS MARKED □,CPK>1.33

7:ALL DIMENSIONS MARKED ▼ MUST BE CONTROLLED BY QC;

8:COMPLIANT TO RoHS&LEAD FREE

9:PART NO.;

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	侧接弹片L2.28×W2.34×H2.30Shielding Clip, SMT		
DWN	xiong	PART NO. TXTB-018B3-0338A	
CHKD	lee	SCALE:1:1	UNIT: mm
APVD	wang	SIZE: A4	SHEET:10F 1
		REV: A4	

CUSTOMER COPY