


客户图

| NO. | ECN NO. | DESCRIPTION | DATE |
|-----|---------|-------------|------|
|     |         |             |      |
|     |         |             |      |



Note:

1: Material (材料):

Barrel: Brass C6801 (针管: 无铅铜 C6801)

Plunger: Brass C6801 (针头: 无铅铜 C6801)

Spring: SUS304 (弹簧: SUS304)

2: Plating (电镀):

Barrel: 3u' Au over 80~120u' Cu over 80~120u' Ni  
(针管: 镀金3u', 铜底80~120u', 镍底80~120u'.)Plunger: 3u' Au over 80~120u' Cu over 80~120u' Ni  
(针头: 镀金3u', 铜底80~120u', 镍底80~120u'.)

Spring: No flash (弹簧: 不电镀)

3: Electrical (电气特性):

Rated Current &amp; Voltage: DC 12V;1A (额定电压&amp;电流: 直流12V,1A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

4: Mechanical (机械性能):

Force: 100g±20% at working height. (100g±20% 在工作高度时)。

Durability: 10.000 cycles(min) (寿命: 10000次)

5: WorkTemperture (工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: -20℃~ +70℃

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



|        |            |            |     |
|--------|------------|------------|-----|
| SCALE: | N/A        | UNIT       | mm  |
| SHEET: | 1 of 1     | PROJECTION |     |
| DATE:  | 2024.10.16 | VER.       | A.0 |

THE UNMARKED TOLERANCE ARE AS BELOW :

| LENGTH |         | ANGLE |        |
|--------|---------|-------|--------|
| X.XX   | ±0.05mm | X.XX  | ±0.50° |
| X.X    | ±0.10mm | X.X   | ±1.00° |
| X.     | ±0.20mm | X.    | ±2.00° |

|              |  |          |                  |
|--------------|--|----------|------------------|
| DESIGNED BY: |  | DWG. NO. | YZP0892-25055-01 |
| CHECKED BY:  |  | TITLE:   | Pogo pin连接器      |
| APPROVED BY: |  |          |                  |