




REV.	ECN NO OR DESCRIPTION	REVISED	DATE



RECOMMENDED PCB LAYOUT
TOLERANCE±0.05(焊盘推荐图)
(FOR REFERENCE ONLY)

Pick Mark



NOTES:

1:MATERIAL:

1-1: STAINLESS STEEL THICKNE=0.08mm

2:FINISH:

2-1:REFER TO THE SPECIFICATION DESCRIPTION TABLE.

3:PRODUCT SPECIFICATIONS:

3-1:RATED CURRENT:1.0A/MAX

3-2:VOLTAGE RATING:1.50V/AC/DC/MAX

3-3: CONTACT RESISTANCE: 80mΩ/MAX

3-4:DURABILITY:1,500 CYCLES.



4:SALT SPRAY:SEE DETAILED LIST

5:PACKING SPECIFICATION:REEL&TARE

6: DIMENSIONS MARKED , CPK > 1.33

7:ALL DIMENSIONS MARKED ▼ MUST BE CONTROLLED BY QC;

8:COMPLIANT TO RoHS&LEAD FREE



UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:

X	:±0.30	X	:±2°
X.X	:±0.20	X.X	:±1°
X.XX	:±0.10		



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	侧贴弹片L2.95×W1.50×H1.65 Shielding Clip,SMT
-------	--

DWN	xiong	PART NO. TXTB-165B1-0301A
-----	-------	---------------------------

CHKD	lee	SCALE:1:1	UNIT: mm	
------	-----	-----------	----------	---

APVD	wang	SIZE: A4	SHEET: 1 OF 1	REV: A4
------	------	----------	---------------	---------

CUSTOMER COPY